

# HSMW-C240

## Mono Color Side View ChipLED

---

### Features

- LED with InGaN chip
- White emitting color
- Compatible with reflow soldering
- Available in 8mm tape and 7" diameter reel


### Applications

- Indicator
- Backlighting

#### **CAUTION!**

This LED is Class 1A ESD sensitive per ANSI/ESDA/JEDEC JS-001. Please observe appropriate precautions during handling and processing. Refer to application note AN-1142 for additional details.

Figure 1: Package Dimensions

**NOTE:**

1. All dimensions in millimeters.
2. Tolerance is  $\pm 0.10\text{mm}$  unless otherwise specified.
3. Dimension in bracket for reference only.

## Absolute Maximum Ratings

Parameters	Value	Unit
DC Forward Current <sup>a</sup>	20	mA
Power Dissipation	70	mW
LED Junction Temperature	95	°C
Operating Temperature Range	-40 to +85	°C
Storage Temperature Range	-40 to +85	°C

a. Derate linearly as shown in Figure 7.

## Optical and Electrical Characteristics ( $T_J = 25^{\circ}\text{C}$ , $I_F = 20\text{mA}$ )

Parameter	Min.	Typ.	Max.	Unit
Luminous Intensity, $I_V$ <sup>a</sup>	285	-	-	mcd
Viewing Angle $2\theta_{1/2}$ <sup>b</sup>	-	150	-	degree
Forward Voltage, $V_F$ <sup>c</sup>	2.5	-	3.5	V
Reverse Current, $I_R$ at $V_R = 5\text{V}$ <sup>d</sup>	-	-	10	$\mu\text{A}$
Thermal Resistance $R\theta_{J-S}$ <sup>e</sup>	-	600	-	$^{\circ}\text{C/W}$

- a. The luminous intensity,  $I_V$  is measured at the mechanical axis of the package and it is tested with a single current pulse condition. The actual peak of the spatial radiation pattern may not be aligned with the axis.
- b.  $\theta_{1/2}$  is the off axis angle where the luminous intensity is  $\frac{1}{2}$  the peak intensity.
- c. Forward voltage tolerance is  $\pm 0.1\text{V}$
- d. Indicate product final test condition. Long term reverse bias is not recommended.
- e. Thermal resistance from LED junction to solder point.

## Bin Information

### Intensity Bin Limits (CAT)

Bin ID	Luminous Intensity (mcd)	
	Min.	Max.
T	285.0	450.0
U	450.0	715.0
V	715.0	1125.0
W	1125.0	1800.0
X	1800.0	2850.0
Y	2850.0	4500.0

Tolerance =  $\pm 15\%$

### Forward Voltage Bin Limits (VF)

Bin ID	Forward Voltage (V)	
	Min.	Max.
Y	2.5	2.7
Z	2.7	2.9
1	2.9	3.1
2	3.1	3.3
3	3.3	3.5

Tolerance =  $\pm 0.1V$

### Color Bin Limits (BIN)

Bin ID	Chromaticity Coordinates	
	x	y
A1	0.2700	0.2455
	0.2700	0.2780
	0.2500	0.2500
	0.2500	0.2175
A2	0.2700	0.2455
	0.2700	0.2130
	0.2500	0.1850
	0.2500	0.2175
B1	0.2700	0.2455
	0.2700	0.2780
	0.2900	0.3060
	0.2900	0.2735
B2	0.2700	0.2455
	0.2700	0.2130
	0.2900	0.2410
	0.2900	0.2735
C1	0.2900	0.3060
	0.3100	0.3355
	0.3100	0.3030
	0.2900	0.2735
C2	0.2900	0.2410
	0.3100	0.2705
	0.3100	0.3030
	0.2900	0.2735
D1	0.3100	0.3030
	0.3100	0.3355
	0.3300	0.3650
	0.3300	0.3325
D2	0.3100	0.3030
	0.3100	0.2705
	0.3300	0.3000
	0.3300	0.3325

Tolerance =  $\pm 0.02$

Figure 2: Chromaticity Diagram




Figure 3: Spectral Power Distribution




Figure 4: Forward Current vs. Forward Voltage




Figure 5: Relative Luminous Intensity vs. Forward Current




Figure 6: Radiation Pattern






Figure 7: Derating Curve




**Figure 8: Recommended Soldering Land Pattern**



**NOTE:**


1. All dimensions in millimeters.
2. Tolerance is  $\pm 0.10\text{mm}$  unless otherwise specified.

### Figure 9: Carrier Tape Dimensions



**NOTE:**

1. All dimensions in millimeters.
2. Tolerance is  $\pm 0.10\text{mm}$  unless otherwise specified.

**Figure 10: Reel Dimensions**


**NOTE:** All dimensions in millimeters.

## Precautionary Notes

### Soldering

- Do not perform reflow soldering more than twice. Observe necessary precautions of handling moisture-sensitive device as stated in the following section.
- Do not apply any pressure or force on the LED during reflow and after reflow when the LED is still hot.
- Use reflow soldering to solder the LED. Use hand soldering only for rework if unavoidable, but it must be strictly controlled to following conditions:
  - Soldering iron tip temperature = 310°C max.
  - Soldering duration = 2sec max.
  - Number of cycles = 1 only
  - Power of soldering iron = 50W max.
- Do not touch the LED package body with the soldering iron except for the soldering terminals, as it may cause damage to the LED.
- Confirm beforehand whether the functionality and performance of the LED is affected by soldering with hand soldering.

Figure 11: Recommended Lead-Free Reflow Soldering Profile



### Handling Precautions

This product has a Moisture Sensitive Level 4 rating per JEDEC J-STD-020. Refer to Broadcom Application Note AN5305, *Handling of Moisture Sensitive Surface Mount Devices* for additional details and a review of proper handling procedures.

- Before use:
  - An unopened moisture barrier bag (MBB) can be stored at <40°C/90% RH for 12 months. If the actual shelf life has exceeded 12 months and the Humidity Indicator Card (HIC) indicates that baking is not required, then it is safe to reflow the LEDs per the original MSL rating.
  - Do not open the MBB prior to assembly (for example, for IQC). If unavoidable, MBB must be properly resealed with fresh desiccant and HIC. The exposed duration must be taken in as floor life.
- Control after opening the MBB:
  - Read the HIC immediately upon opening of MBB.
  - Keep the LEDs at <30°/60%RH at all times, and complete all high temperature-related processes, including soldering, curing or rework within 72 hours.
- Control for unfinished reel:
 

Store unused LEDs in a sealed MBB with desiccant or a desiccator at <5%RH.
- Control of assembled boards:
 

If the PCB soldered with the LEDs is to be subjected to other high-temperature processes, store the PCB in a sealed MBB with desiccant or desiccator at <5% RH to ensure that all LEDs have not exceeded their floor life of 72 hours.
- Baking is required if:
  - The HIC indicator indicates a change in color for 10% and 5%, as stated on the HIC.
  - The LEDs are exposed to conditions of >30°C/60% RH at any time.
  - The LED's floor life exceeded 72 hours.

The recommended baking condition is: 60±5°C for 20 hours.

Baking can only be done once.



## Application Precautions

- The drive current of the LED must not exceed the maximum allowable limit across temperature as stated in the data sheet. Constant current driving is recommended to ensure consistent performance.
- Circuit design must cater to the whole range of forward voltage ( $V_F$ ) of the LEDs to ensure the intended drive current can always be achieved.
- The LED exhibits slightly different characteristics at different drive currents, which may result in a larger variation of performance (meaning: intensity, wavelength, and forward voltage). Set the application current as close as possible to the test current to minimize these variations.
- If the LED is intended to be used along with LED of other color to achieve color mixing, Broadcom does not guarantee the consistency of the resultant color. Do contact Broadcom Sale Representative for such application.
- The LED is not intended for reverse bias. Use other appropriate components for such purposes. When driving the LED in matrix form, ensure that the reverse bias voltage does not exceed the allowable limit of the LED.

- Avoid rapid change in ambient temperature, especially in high-humidity environments, because they cause condensation on the LED.
- If the LED is intended to be used in harsh or outdoor environment, protect the LED against damages caused by rain water, water, dust, oil, corrosive gases, external mechanical stresses, and so on.

## Eye Safety Precautions

LEDs may pose optical hazards when in operation. Do not look directly at operating LEDs because it might be harmful to the eyes. For safety reasons, use appropriate shielding or personal protective equipment.

## Disclaimer

Broadcom's products and software are not specifically designed, manufactured, or authorized for sale as parts, components, or assemblies for the planning, construction, maintenance, or direct operation of a nuclear facility or for use in medical devices or applications. The customer is solely responsible, and waives all rights to make claims against Broadcom or its suppliers, for all loss, damage, expense, or liability in connection with such use.

Broadcom, the pulse logo, Connecting everything, Avago Technologies, Avago, and the A logo are among the trademarks of Broadcom and/or its affiliates in the United States, certain other countries and/or the EU.

Copyright © 2019 by Broadcom. All Rights Reserved.

The term "Broadcom" refers to Broadcom Limited and/or its subsidiaries. For more information, please visit [www.broadcom.com](http://www.broadcom.com).

Broadcom reserves the right to make changes without further notice to any products or data herein to improve reliability, function, or design. Information furnished by Broadcom is believed to be accurate and reliable. However, Broadcom does not assume any liability arising out of the application or use of this information, nor the application or use of any product or circuit described herein, neither does it convey any license under its patent rights nor the rights of others.



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Broadcom Limited:](#)

[HSMW-C240](#)