

5

4

3

2

1

DRAWING NO.

CPMC782-CUST

## REVISIONS

01	OFFICAL RELEASE			
	03-05-09	Z G	B Y	T
02	RELEASE FOR SUPPLIER ALTER			
	07-27-11	Y G	Y G	M L
03	MATERIAL: BODY WAS BRASS DIMENSIONS: $\Phi 14.3 \pm 0.3$ WAS $\Phi 14.5$ $7.2 \pm 0.2$ WAS $7.60$ ; $9.6 \pm 0.3$ WAS $9.70$ $\Phi 0.86 \pm 0.05$ WAS $\Phi 0.96$ ADD CABLE STRIP DIMENSIONS			
	12-31-11	Y G	Y G	M L
04	MATERIAL: BODY WAS ZINC INSULATOR WAS TEFLON			
	02-10-12	Y G	Y G	M L

Description: Plug Assembly, Straight Crimp Type BNC 75 Ohm, RG59, 62

Part No: CPMC782

Application: For Cable BELDEN 1505A, RG59, 62

Crimp Tool: 24-9959P

Impedance: 75 Ohms

Fequency Range: 0-2 GHz

Material: Body Brass Nickel Plated

Contact Brass Gold Plated



Insulator POM

Crimp Sleeve Brass Nickel Plated

Coupling Nut Zinc Nickel Plated

RoHS Compliance: Yes

Technical Detail: Refer to Emerson Document P/N 27-0000



CABLE STRIP DIMENSIONS

## DIM OUTLINE

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY	DATE
DECIMALS	mm	YUGE HU	07-27-11
X	± 0.5	CHECKED BY	DATE
X.X	± 0.2	YUGE HU	07-27-11
X.XX	± 0.1	APPROVED BY	DATE
ANGLES	± 0.5°	LIN MA	07-27-11
		U/M	mm

THIS DRAWING WAS PRODUCED BY COMPUTER, DO NOT SCALE DRAWING OR UPDATE MANUALLY.

		Connectivity Solutions	
		TITLE	
SHEET		DRAWING NO.	
1 OF 1		CPMC782-CUST	
		SIZE	
		A	

SHEET	DRAWING NO.	SIZE
1 OF 1	CPMC782-CUST	A

5

4

3

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[CPMC-78-2](#)