








SMD POWER INDUCTORS



- Features

1. Open frame construction.
2. Low DCR
3. Excellent Power Density
4. Engineered to Provide High Efficiency

CHARACTERISTICS

[illegible]

(1). Inductance tolerance for 0.12uH~0.47uH: $\pm 30\%$, for 1.0uH~4.7uH: $\pm 20\%$, for 10uH~100uH: $\pm 10\%$. Tested at 0.25V, 0ADC and 25°C

(2). DCR measured at 25°C.

(3). The DC current at which the inductance decreases by 10% from its initial value.

(4). The DC current that results in a 40°C temperature rise from 25°C ambient.

[Click here for QUANTITY PER REEL & PACKING INFORMATION](#)

Custom versions available upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SC1206-R47](#) [SC1206-4R7](#) [SC1206-R22](#) [SC1206-100](#) [SC1206-R12](#) [SC1206-101](#) [SC1206-470](#) [SC1206-1R0](#)
[SC1206-2R2](#) [SC1206-220](#)