




D

C

B

A



REAR VIEW

DRAWING REVISIONS (RELEASE DATE ON FILE)			
REV	DOCUMENT	APP	APPROVAL DATE
E	PER C.O.# 851	V.R.	02/09/10

D

C

B

A

2.6 REF
[.10]
SECONDARY LOCK SHIPPED
IN PRE-STAGED POSITION

INSULATOR COLOR: BLACK
(POLYAMIDE BASED
ALLOY GLASS-FILLED)

DATE CODE


BACK PLATE
COLOR: BLACK
(GLASS-FILLED POLYESTER)

NOTES:

1. ALL DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES.
2. FOR WIRE SIZE APPLICATION, CONSULT FACTORY.
3. FEMALE TERMINAL ORDERED SEPARATELY: 425 00 00 873/872.
4. MATES WITH CINCH HEADER CONNECTOR (CONSULT FACTORY).
5. SEAL PLUG ORDERED SEPARATELY: 581 00 00 011.
6. TOLERANCES UNLESS OTHERWISE SPECIFIED:
.X ±0.5
.XX ±0.25
7. SEALING RANGE FOR WIRE INSULATION DIA.:
MAX 2.64MM (.104"), MIN 1.96MM (.077").
8. A TRIANGLE "▲" INDICATES CRITICAL FUNCTION DIMENSION.
9. IF TIE-WRAP DRESSING CONDUCTORS, CINCH RECOMMENDS A SPACING
OF NO LESS THAN 2 INCHES BEHIND THE BACK PLATE.

JACKSCREW, STEEL
10-24 UNC THREAD
(YELLOW TRIVALENT CHROMATE)

SECONDARY LOCK
COLOR: WHITE
(GLASS-FILLED POLYESTER)

UNITS				PRO/E		CINCH		MODELED BY: J. DRYE			
DO NOT SCALE DRAWING		DESIGN ENGINEER		DATE		TITLE					
UNLESS OTHERWISE SPECIFIED: ALL DIMENSIONS ARE IN mm		A. CAINES		05/03/01		CONNECTOR ASSEMBLY SOCKET 30 POSITION					
CONFIDENTIAL THIS DOCUMENT IS THE PROPERTY OF CINCH. NEITHER THIS DOCUMENT NOR ANY OF THE INFORMATION CONTAINED IN IT MAY BE DUPLICATED OR DISCLOSED WITHOUT PRIOR WRITTEN CONSENT OF CINCH. ©COPYRIGHT 2010 CINCH		APPROVALS ON FILE				MATERIAL		CONTROL SPEC NUMBER			
						SEE VIEW		POLAR B			
						MATERIAL SPEC NUMBER		FINISH		PROJECT NUMBER	
						-		-		A14243	
						CAD FILE NUMBER		DRAWING NUMBER			
						5810130028S		5810130028S			
						CAGE IDENT NO.		SIZE			
						71785		B			
						SCALE		1.500			
								SHEET 1 OF 1			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[581-01-30-028](#)