




NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:

- 1.1 BODY: (133-9711-201 & -202) GOLD PLATED COPPER ALLOY
(133-9711-204 & 205) SILVER PLATED COPPER ALLOY
- 1.3 INSULATOR: PTFE (TEFLON)
- 1.4 CENTER CONTACT: (133-9711-201 & -202) GOLD PLATED BERYLLIUM COPPER
(133-9711-204 & 205) SILVER PLATED BERYLLIUM COPPER

2. ELECTRICAL SPECIFICATIONS:

- 2.1 IMPEDANCE: 50 OHMS
- 2.2 FREQUENCY RANGE: 0 - 6 GHz
- 2.3 WORKING VOLTAGE: 335 VRMS MAX AT SEA LEVEL
- 2.4 DIELECTRIC WITHSTANDING VOLTAGE: 1000 VRMS MIN AT SEA LEVEL
- 2.5 INSULATION RESISTANCE: 1000 MEGOHM MIN
- 2.6 CONTACT RESISTANCE:
 - CENTER CONTACT - INITIAL 5 MILLIOHM MAX, AFTER ENVIRONMENTAL 8 MILLIOHM MAX
 - OUTER CONDUCTOR - INITIAL 1 MILLIOHM MAX, AFTER ENVIRONMENTAL 1.5 MILLIOHM MAX
- 2.7 CORONA LEVEL: 250 VOLTS MIN AT 70,000 FEET
- 2.8 RF HIGH POTENTIAL WITHSTANDING VOLTAGE: 600 VRMS AT 4 AND 7 MHz

3. MECHANICAL SPECIFICATIONS:

- 3.1 ENGAGE/DISENGAGE FORCE: 5.6 LBS MAX ENGAGEMENT
1.0/8.0 LBS MIN/MAX DISENGAGEMENT
- 3.2 CONTACT RETENTION FORCE: 2.0 LBS MIN
- 3.3 DURABILITY: 500 CYCLES MIN





4. ENVIRONMENTAL:

- 4.1 (MEETS OR EXCEEDS THE APPLICABLE PARAGRAPH OF MIL-PRF-39012)
- 4.2 THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION F
- 4.3 OPERATING TEMPERATURE: -65 DEG C TO 165 DEG C
- 4.4 CORROSION: MIL-STD-202, METHOD 101, CONDITION B
- 4.5 SHOCK: MIL-STD-202, METHOD 213, CONDITION B
- 4.6 VIBRATION: MIL STD-202, METHOD 204 CONDITION B
- 4.7 MOISTURE : MIL STD-202, METHOD 106

5. PACKAGING:

- 5.1 133-9711-201 & -204: BAGGED
- 5.2 133-9711-202 & -205: TAPE AND REEL PACKAGED, 750 PIECES PER REEL,
16MM X 12MM PITCH TAPE WITH COVER TAPE DOT PER FIG. 1.

6. CONNECTOR MARKED "NM" FOR NON-MAGNETIC.



*NOTE: THIS PATTERN IS FOR REFERENCE ONLY.
PATTERN MAY VARY DEPENDING ON
ASSEMBLY PROCESS, BOARD TYPE, OR
SPECIFIC ELECTRICAL OR MECHANICAL
REQUIREMENTS.

 This PROPRIETARY Document is property of Cinch Connectivity Solutions. It is confidential in nature, non-transferable, and issued with the clear understanding that it is no traced or copied without permission and is returnable upon demand. INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2009.	3RD ANGLE PROJECTION		JOHNSON			
	RoHS2 ☒ 2011/65/EU		Title: JACK ASSY STRAIGHT SURFACE MOUNT NON-MAGNETIC, MCX			
	UNLESS OTHERWISE SPECIFIED UNITS: INCH		Model No. 133-9711-201/210			
	Size B		DO NOT SCALE DRAWING	Date 7/29/2016	Sheet 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[133-9711-201](#)