

RED INDICATES ORIGINAL

DWG
SIZE
B

DATA CONTAINED IN THIS DOCUMENT IS
PROPRIETARY TO TROMPETER ELECTRONICS INC.
AND SHALL NOT BE DISCLOSED, COPIED OR USED
FOR PROCUREMENT OR MANUFACTURE WITHOUT
EXPRESS WRITTEN PERMISSION.

REVISIONS




3-0122

SH 1

REV	EO	DESCRIPTION	DWN	APPROVED	DATE
B	10716	GENERAL UPDATE AND CORRECTED VIEWS ON SHEETS 1 & 2; SEE ECD	DKC	<i>bm; fa</i>	6/27/94

DASH NO	MODEL NO	CENTER & INTMD CONTACT TYPE
-1	BJ3450P	SOCKET/PIN
-2	BJ3450S	PIN/SOCKET

INCH	MM	INCH	MM
.010	0.25	.278	7.06
.026	0.66	.330	8.38
.03	0.76	.335	8.51
.075	1.91	.437	11.10
.093	2.36	.510	12.95
.125	3.18	.717	18.21
.240	6.10	.750	19.05
.274	6.96	.795	20.19
		1.03	26.16



6. EXAMPLE OF COMPLETE MODEL NO:

BJ3450 P
BASIC MODEL NO CENTER & INTERMEDIATE
CONTACT TYPE
(SEE TABLE)

RECOMMENDED
PANEL CUTOUT

5 MAX PNL THK .125 WITH EITHER LOCKWASHER
OR WAVE WASHER

4 SOLDER PNT ACCEPTS .026 MAX DIA CONDUCTOR

3. CONCENTRIC TWINAX NONINSULATED BULKHEAD MOUNT
RECEPTACLE, SOCKET CENTER CONTACT AND PIN INTERMEDIATE
CONTACT OR PIN CENTER CONTACT AND SOCKET INTERMEDIATE CONTACT

2. FINISH: TFS-III (500 HOURS SALT SPRAY)

1. ALL DIM ARE IN INCHES

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED .XX ± .03 .XXX ± .010 .XXXX ± .005 ANGLES ±	TROMPETER RF connectivity a cinch connectivity solutions brand	BJ3450P/S	
DWN DKC 6-16-94	MATERIAL	CODE IDENT	DRAWING NO.
CHK <i>bm</i> 6-24-94		14949	3-0122
ENGR			REV B
NEXT ASSY	APPR <i>fa</i> 6/27/94	SCALE 4/1	DATE 12-7-87
			SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[BJ3450P](#)