

For stripping and assembly instnuctions see Drawing Number: VAIF1301

Electrical Characteristics

Nominal Impedance:	Non Constant
Frequency Range:	DC to 2 GHz
VSWR:	1.35:1 maximum
Operating Voltage (rms):	250 V maximum at sea level


Mechanical Characteristics

Mating Cycles:	200 cycles minimum
----------------	--------------------

Environmental Characteristics

Temperature Range:	-55 °C to +85 °C
--------------------	------------------

	PART	DESCRIPTION		
1	Body	Brass, nickel plated		
Altered Measurments		KA	4	12 Oct 07
CAD Issue		SN	3	12 Sep 02
Up Issue		SN	2	20 Feb 01
First Issue		SN	1	31 Jul 00
DESCRIPTION OF REVISION		APPVD	ISS	DATE

 Cinch Connectivity Solutions 7-13 Russel Way, Widford Industrial Estate, Chelmsford, Essex, CM1 3AA, UK. Tel: +44 (0) 1245 359515 Fax: +44 (0) 1245 358938	SCALE: Not To Scale	DRAWN BY:	S Nash	TITLE: F Twist-On Plug for RG59	PART NUMBER:	
	DIMENSIONS: mm	CHECKED BY:	P Couzens		TOF59	
	TOLERANCES: ± 0.2mm unless otherwise stated	APPROVED BY:	P Couzens		PAGE: 1 of 1	
		DATE:	12 Sep 02			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[TOF59](#)