


- NOTES:
- 1.0 ELECTRICAL SPECIFICATIONS:
- 1.1 FREQUENCY RANGE: DC to 2500 MHz
- 1.2 OPERATING RF INPUT POWER LEVEL: 1 WATT MAX.
- 1.3 MAIN RF PATH ATTENUATION: 0.5 ±0.15dB
- 1.4 SAMPLED PORT COUPLING: 26 ±1.2dB
- 1.5 VSWR: 1.20:1 MAX.
- 2.0 FINISH
- 2.1 GREY PER MIL-E-15090 TYPE II , CLASS 2
OVER MIL-C-5541 CLASS 3A
MEETS MIL-F-14072
MEETS MIL-E-5400
- 3.0 MARKING: MARK UNIT AS SHOWN.
SLK-08216-82-01
- 4.0 DIMENSIONS IN PARENTHESIS ARE
IN MILLIMETERS.



MODEL NUMBER	REV.
RFM-7020-26-NNN-79	-

REV.	DESCRIPTION	DATE
-	RELEASED	2/3/04

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±1°		FSCM NO. 34078	MIDWEST MICROWAVE	
		NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Midwest Microwave		TITLE RF SIGNAL SAMPLER
DRAWN/DATE S.ORLOV 2/3/04		ENG./DATE P.GOODMAN 2/3/04		DRAWING NUMBER RFM-7020-26-NNN-79
CHECKED/DATE		APPROVED/DATE		SCALE: 2=1 SHEET 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[RFM-7020-26-NNN-79](#)