

PART NUMBER
148-0801-801

REV	ECO	DATE
1	INITIAL RELEASE	17AUG2021

NOTES:

1. MATERIAL AND FINISH:


- 1.1 BODY: STAINLESS STEEL, PASSIVATED
- 1.2 CONTACT: BERYLLIUM COPPER, GOLD PLATE
- 1.3 INSULATOR: ULTEM 1000, AMBER
- 1.4 GASKET: SILICONE, RED



2. ELECTRICAL SPECIFICATIONS:

- 2.1 IMPEDANCE: 50 OHMS NOMINAL
- 2.2 FREQUENCY RANGE: DC~67 GHz
- 2.3 VSWR: 1.30 MAX

3. MECHANICAL SPECIFICATIONS:

- 3.1 ENGAGE/DISENGAGE FORCE: 0.23 Nm MAX (1.85MM)
- 3.2 COUPLING NUT RETENTION: 267 N MIN
- 3.3 COUPLING PROOF TORQUE: 1.65 Nm MIN
- 3.4 DURABILITY: 500 CYCLES MIN



 cinch CONNECTIVITY SOLUTIONS a bell group	Model No: 148-0801-801		JOHNSON		
	RoHS <input checked="" type="checkbox"/> CEP/2015/863 COMPLIANT <small>UNLESS OTHERWISE SPECIFIED UNITS: INCH</small> .XXX±.008 .XXXX±.004 ANGLES±5°	Cage Code	Title: 1.85MM TERMINATION, PLUG, WITHOUT CHAIN		
			Drawing No.	148-0801-801	REV. 1
			Drawn by: TOMMY REN Date: 08/17/2021	Size B DO NOT SCALE DRAWING	Workmanship Std/Sheet NONE 1 OF 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[148-0801-801](#)