


TIP140 TIP141 TIP142 NPN
TIP145 TIP146 TIP147 PNP

**SILICON POWER DARLINGTON
COMPLEMENTARY TRANSISTORS**



TO-218 TRANSISTOR CASE

MAXIMUM RATINGS: ($T_C=25^\circ\text{C}$)

Collector-Base Voltage	V_{CBO}	60	80	100	V
Collector-Emitter Voltage	V_{CEO}	60	80	100	V
Emitter-Base Voltage	V_{EBO}		5.0		V
Continuous Collector Current	I_C		10		A
Peak Collector Current	I_{CM}		20		A
Base Current	I_B		0.5		A
Power Dissipation	P_D		125		W
Operating and Storage Junction Temperature	T_J, T_{stg}		-65 to +150		$^\circ\text{C}$
Thermal Resistance	Θ_{JC}		1.0		$^\circ\text{C/W}$

ELECTRICAL CHARACTERISTICS: ($T_C=25^\circ\text{C}$ unless otherwise noted)

SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	UNITS
I_{CBO}	$V_{CB}=\text{Rated } V_{CBO}$			1.0	mA
I_{CEO}	$V_{CE}=\frac{1}{2} \text{ Rated } V_{CEO}$			2.0	mA
I_{EBO}	$V_{EB}=5.0\text{V}$			2.0	mA
BV_{CEO}	$I_C=30\text{mA}$ (TIP140, TIP145)	60			V
BV_{CEO}	$I_C=30\text{mA}$ (TIP141, TIP146)	80			V
BV_{CEO}	$I_C=30\text{mA}$ (TIP142, TIP147)	100			V
$V_{CE(SAT)}$	$I_C=5.0\text{A}, I_B=10\text{mA}$			2.0	V
$V_{CE(SAT)}$	$I_C=10\text{A}, I_B=40\text{mA}$			3.0	V
$V_{BE(ON)}$	$V_{CE}=4.0\text{V}, I_C=10\text{A}$			3.0	V
V_F	$I_F=10\text{A}$			2.8	V
h_{FE}	$V_{CE}=4.0\text{V}, I_C=5.0\text{A}$	1000			
h_{FE}	$V_{CE}=4.0\text{V}, I_C=10\text{A}$	500			
t_{on}	$I_C=10\text{A}, I_{B1}=I_{B2}=40\text{mA}, R_L=3.0\Omega$		0.9		μs
t_{off}	$I_C=10\text{A}, I_{B1}=I_{B2}=40\text{mA}, R_L=3.0\Omega$		4.0		μs

R2 (1-August 2008)

CentralTM

Semiconductor Corp.

DESCRIPTION:


The CENTRAL SEMICONDUCTOR TIP140, TIP145 series types are Complementary Silicon Power Darlington Transistors manufactured by the epitaxial base process, designed for general purpose amplifier and low speed switching applications where high gain is required.

MARKING: FULL PART NUMBER

	TIP140	TIP141	TIP142	
SYMBOL	TIP145	TIP146	TIP147	UNITS
V_{CBO}	60	80	100	V
V_{CEO}	60	80	100	V
V_{EBO}		5.0		V
I_C		10		A
I_{CM}		20		A
I_B		0.5		A
P_D		125		W
T_J, T_{stg}		-65 to +150		$^\circ\text{C}$
Θ_{JC}		1.0		$^\circ\text{C/W}$

**SILICON POWER DARLINGTON
COMPLEMENTARY TRANSISTORS**

TO-218 TRANSISTOR CASE - MECHANICAL OUTLINE



SYMBOL	DIMENSIONS			
	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.185	0.193	4.70	4.90
B	0.075	0.082	1.91	2.08
C	0.098		2.49	
D	0.019	0.030	0.48	0.76
E	0.578	0.598	14.68	15.19
F	1.220		30.99	
G	0.708		17.98	
H	-	0.637	-	16.18
J	-	0.480	-	12.19
K	0.155	0.163	3.94	4.14
L	0.043	0.051	1.09	1.30
M	0.425	0.437	10.80	11.10
N	0.157	0.161	3.99	4.09

LEAD CODE:

- 1) BASE
- 2) COLLECTOR
- 3) EMITTER

Note: Tab is common to lead 2.

MARKING:

FULL PART NUMBER

TO-218 Transistor (REV: R0)

R2 (1-August 2008)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Central Semiconductor:](#)

[TIP147](#)