


DATE	REV	ECN	APP'D. BY
03/08/18	A0	Released	TM

ISOMETRIC VIEW


JACK HOUSING

INSERT MODULE




WIRE CAP

WIRING LABEL



IDC MODULE



TRANSMISSION PERFORMANCE

Meet all requirements specified in connecting hardware requirement of:
ANSI/TIA-568-C.2, Category 5e

ELECTRICAL

Electrical Insulation Resistance : 500 MΩ
min. @ 100V d.c
Dielectric Withstanding Voltage : 1000V d.c. or
a.c. Peak Contact to Contact @ 60Hz for 1
minute


MECHANICAL

Insertion / Extraction Life : 750 Cycles Minimum
IDC Wire Gauge : 22 ~ 24 AWG

PHYSICAL

Housing : High-Impact, Flame-Retardant Plastic,
UL 94V-0
Spring Wire : Phosphor Bronze Alloy Plated With
50 micro-inch of Gold
IDC : Phosphor Bronze Alloy With 100
micro-inch 100% Sn Alloy

ASSEMBLY DIMENSION




COMPONENTS

ITEM	DISCRIPTION	Q'TY
5	WIRING LABEL	2
4	IDC MODULE	1
3	WIRE CAP	1
2	INSERT MODULE	1
1	JACK HOUSING	1

SS-82000-005

PART NUMBER

THIRD ANGLE PROJECTION




DO NOT SCALE DRAWING

DRAWING IS SUBJECT TO
CHANGE WITHOUT NOTICE

DIMENSIONS: METRIC

UNLESS OTHERWISE SPECIFIED
TOLERANCES ARE ±0.2
ANGLES ARE ± 1°

SHEET NO. 1 OF 1

RoHS
2002/95/EC

bel

206 Van Vorst Street
Jersey City, NJ 07302
+1 201 432 0463
<http://www.belfuse.com>

TITLE:

CAT 5e UNSHIELDED TOOL-LESS KEYSTONE JACK

DRN BY: DG DATE 03/06/18

APPD BY: TM DATE 03/08/18

DWG NO. CT820021 REV. A0

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON
ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF
BEL FUSE, INC. AND SHALL NOT BE REPRODUCED,
COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN
CONSENT OF BEL FUSE, INC.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bel:](#)

[SS-82000-005](#)