




TOP VIEW




SIDE VIEW



BOTTOM VIEW



Specifications			Notes	Revision History						
Description	Value	Unit		Version	Description		Date	Approved		
Technology	Electro-Mechanical		1) All dimensions are in mm unless otherwise noted 2) All parts meet RoHS	1	Released from Engineering		10/21/2013	J.S		
Resonant Frequency	2,048	(Hz)								
Rated Voltage	12	(V)								
SPL @ 10cm	85	(dBA)								
Coil Resistance	115	(ohm)								
Mount Type	Thru-hole									
Voltage Range	6 ~ 18	(V)								
Max Rated Current	40	(mA)								
Housing Material	NORYL									
Operating Temperature	-25 ~ +70	°C								
Storage Temperature	-30 ~ +80	°C								
Weight	7	(g)								
 DB UNLIMITED				Electro-Mechanical Transducer		TE162012-2				
				Drawn by		Date	Checked by	Date	Approved by	Date
			A.B.		10/21/2013	C.E.	10/21/2013	J.S	10/21/2013	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[DB Unlimited:](#)

[TE162012-2](#)