



REV	ECO	DATE
F	23394	3/17/2011
G	57925	4/30/2021
H	58847	11/20/2023



NOTES: UNLESS OTHERWISE SPECIFIED.

1. MATERIAL & FINISH:

- 1.1 HOUSING: PASSIVATED STAINLESS STEEL
- 1.2 SUPPORT BEAD: ULTEM 1000
- 1.3 CENTER CONTACT: GOLD PLATED BERYLLIUM COPPER

2. SPECIFICATIONS:

- 2.1 FREQUENCY RANGE: DC-30.0 GHz
- 2.2 IMPEDANCE: 50 OHMS NOMINAL
- 2.3 VSWR (MAX)
 - 2.3.1 DC TO 20 GHz: 1.10:1
 - 2.3.2 20 TO 26.5 GHz: 1.15:1
- 2.4 TYPICAL VSWR FROM 26.5 TO 30.0 GHz: 1.20:1
- 2.5 OPERATING TEMP. RANGE: -65°C TO +125°C

<p>NOTICE: The information in this drawing is PROPRIETARY and must not be used without the permission of Cinch Connectivity Solutions. It may contain data whose export is restricted. Verify status prior to exporting.</p> <p>INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.5-2018</p>	Model No:	ADT-2735-FF-3MM-02		MIDWEST MICROWAVE	
	RoHS2	<input checked="" type="checkbox"/>	2011/65/EU	Title: 3.5mm FEMALE TO FEMALE ADAPTER	
	UNLESS OTHERWISE SPECIFIED	3RD ANGLE PROJECTION	ENGINEER: A. OSGA	Drawing No.	REV.
	UNITS: INCH	Date: 11/20/1992	Size: A	DO NOT SCALE DRAWING	ADT-2735-FF-3MM-02-01 H

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[ADT-2735-FF-3MM-02](#)