


Features

- ◆ Ultra wide 4:1 input voltage range
- ◆ Single output voltage models from 1.8 to 15 VDC
- ◆ Dual output voltage models
- ◆ Extended operating temperature range: -40°C to 85°C
- ◆ Under voltage lockout
- ◆ Remote On/Off
- ◆ Shielded metal case with insulated baseplate
- ◆ Optional heatsink
- ◆ Lead free design - RoHS compliant
- ◆ 3-year product warranty



The TEN 30WI series is a family of high performance 30W dc-dc converters featuring ultra wide 4:1 input voltage ranges in a compact low profile package with industry-standard footprint. A very high efficiency allows operating temperatures up to 85°C. A built-in filter for both input and output minimizes the need for external filtering. Further standard features include remote On/Off, output voltage trimming, over voltage protection, under voltage lockout and short circuit protection. Typical applications for these products are battery operated equipment and distributed power architectures in communication and industrial electronics, everywhere where isolated, tightly regulated voltages are required and space is limited on the PCB.

Models

Order code	Input voltage range	Output voltage	Output current max.	Efficiency typ.
TEN 30-2408WI	10 – 40 VDC (nominal 24 VDC)	1.8 VDC	8'000 mA	80 %
TEN 30-2409WI		2.5 VDC	8'000 mA	85 %
TEN 30-2410WI		3.3 VDC	6'000 mA	87 %
TEN 30-2411WI		5.0 VDC	6'000 mA	87 %
TEN 30-2412WI		12 VDC	2'500 mA	87 %
TEN 30-2413WI		15 VDC	2'000 mA	88 %
TEN 30-2422WI		±12 VDC	±1'250 mA	85 %
TEN 30-2423WI		±15 VDC	±1'000 mA	86 %
TEN 30-4808WI	18 – 75 VDC (nominal 48 VDC)	1.8 VDC	8'000 mA	81 %
TEN 30-4809WI		2.5 VDC	8'000 mA	86 %
TEN 30-4810WI		3.3 VDC	6'000 mA	87 %
TEN 30-4811WI		5.0 VDC	6'000 mA	88 %
TEN 30-4812WI		12 VDC	2'500 mA	87 %
TEN 30-4813WI		15 VDC	2'000 mA	88 %
TEN 30-4822WI		±12 VDC	±1'250 mA	86 %
TEN 30-4823WI		±15 VDC	±1'000 mA	87 %

Input Specifications

Input current at no load (nominal input 24/48 Vin)	1.8 Vout models: 2.5/3.3 Vout models: other models:	35 / 20 mA typ. 40 / 25 mA typ. 70 / 45 mA typ.
Input current at full load (nominal input 24/48 Vin)	1.8 Vout models: 2.5/3.3 Vout models: other models:	760 / 380 mA typ. 1030 / 510 mA typ. 1500 / 750 mA typ.
Input voltage variation (dv/dt)		5 V/ms, max. (complies with ETS 300 132 part. 4.4)
Under voltage lockout	24 Vin models: 48 Vin models:	7 VDC min. / 8 VDC typ. / 9.2 VDC max. 15 VDC min. / 16 VDC typ. / 17.5 VDC max.
Surge voltage (100 msec. max.)	24 Vin models: 48 Vin models:	50 V max. 100 V max.
Conducted noise (input)		EN 55022 level A, FCC part 15, level A (with external components)
	Please refer to Application note:	www.tracopower.com/overview/ten30wi
ESD (input)		EN 61000-4-2, perf. criteria B
Fast transient (input)		EN 61000-4-4, perf. criteria A
Surge (input)		EN 61000-4-5, perf. criteria B

Output Specifications

Voltage set accuracy		±1 %
Output voltage adjustment		±10 %
Regulation	– Input variation Vin min. to Vin max. – Load variation 10 – 100 %:	±0.5 % max. single output models: ±0.5 % max. dual output models: ±1.0 % max. (balanced load) ±5 % max. (load cross variation 25 % / 100 %)
Temperature coefficient		±0.02 %/K
Ripple and noise (20 MHz Bandwidth):		75 mVpk-pk max.
Start up time (nominal Vin and constant resistive load)		10 ms typ.
Transient response setting time (25% load step change)		300 µs typ.
Short circuit protection		indefinite (automatic recovery)
Over load protection		150 % of Iout max typ. foldback
Thermal shutdown		at +115°C typ
Over voltage protection	1.8, 2.5 & 3.3 V output models: 5.0 V output models: 12 V output models: 15 V output models:	3.9 V 6.2 V 15 V 18 V
Minimum load (only for dual output models)		10% of rated max current (operation at lower load condition will not damage these converters, however, they may not meet all listed specifications)
Capacitive load	1.8 / 2.5 Vout models: 3.3 / 5.0 Vout models: 12 / 15 Vout models: ±12 / ±15 Vout models:	65'000 µF max./ 33'000 µF max. 19'500 µF max./ 10'200 µF max. 3'300 µF max./ 1'100 µF max. ±1'000 µF max./ ±680 µF max. (per output)

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.


General Specifications

Temperature ranges	– Operating – Case temperature – Storage	–40°C to +85°C (with derating) +100°C max. –55°C to +105°C
Thermal impedance	– with heat-sink TEN-HS2 – without heat-sink	8.24 K/Watt 10 K/Watt
Humidity (non condensing)		95 % rel H max.
Reliability, calculated MTBF (MIL-HDBK-217F, at +25°C, ground benign)		>750'000 h
Isolation voltage (60sec.)	– Input / Output	1'500 VDC
Isolation resistance	– Input / Output	>1'000 M Ohm
Isolation capacitance	– Input / Output	1000 pF max.
Remote On/Off	– On: – Off: – Off idle current:	3.5 ... 12 VDC or open circuit. 0 ... 1.2 VDC or short circuit pin 3 and pin 2 3 mA typ.
Switching frequency		300 kHz typ. (pulse width modulation PWM)
Vibration		10–55 Hz, 2G, 30 minutes along X,Y,Z
Safety approvals		UL 60950, IEC/EN 60950, compliance UL 62368-1 up to 60 VDC input voltage (SELV limit) www.tracopower.com/overview/ten30wi
Environmental compliance	– Reach – RoHS	www.tracopower.com/info/reach-declaration.pdf RoHS directive 20011/65/EU

Supporting documents: www.tracopower.com/overview/ten30wi

Output Voltage Adjustment


Trim up



Ru [kohm]*

output	1.8V	2.5V	3.3V	5.0V
+5%	1.2	4.3	6.8	4.7
+10%	0.068	0.82	1.5	0.56
output	12V	15V	±12V	±15V
+5%	47	47	27	33
+10%	8.2	6.8	2.2	2.7

Trim down



Rd [kohm]*

output	1.8V	2.5V	3.3V	5.0V
–5%	1.8	6.8	8.2	5.6
–10%	0.1	0.82	0.68	0.68
output	12V	15V	±12V	±15V
–5%	56	56	33	39
–10%	5.6	2.2	2.7	3.3


*approximate values

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Physical Specifications

Casing material	copper, nickel plated
Baseplate material	none conductive FR4
Potting material	epoxy (UL 94V-0 -rated)
Weight	48 g (1.69 oz)
Soldering temperature	max. 265°C / 10 sec.

Outline Dimensions



Pin-Out

Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	Remote On/Off	
4	No pin	+Vout
5	+Vout	Common
6	-Vout	-Vout
7	Trim	




Dimensions in [mm], () = Inch

Pin diameter: 1.0 ±0.05 (0.02 ±0.002)

Pin pitch tolerances: ±0.35 (±0.014)

Case tolerances: ±0.5 (±0.02)

Heat-sink TEN-HS2




Order code: TEN-HS2

(cont.: heat-sink, thermal pad, 2 clamps)

Material: Aluminum

Finish: Anodic treatment (black)

Weight: 19 g (0.67oz) (without converter)



Note:

The product label on converter has to be removed before mounting the heat-sink. For volume orders converters will be supplied with heat-sinks already mounted. Please contact factory for quotation. Separate heat-sinks are only available for prototypes and small quantity orders.

Specifications can be changed without notice! Make sure you are using the latest documentation, downloadable at www.tracopower.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TRACO Power:

[TEN 30-4811WI](#) [TEN 30-2412WI](#) [TEN 30-2410WI](#) [TEN 30-2413WI](#) [TEN 30-2411WI](#) [TEN 30-4810WI](#) [TEN 30-4808WI](#) [TEN 30-4822WI](#) [TEN 30-2423WI](#) [TEN 30-4823WI](#) [TEN 30-2422WI](#) [TEN 30-4812WI](#) [TEN 30-2409WI](#) [TEN 30-4809WI](#) [TEN 30-2408WI](#) [TEN 30-4813WI](#)