


Features

- ◆ High power density: 40 W in a 51x51x10mm (2"x2"x0.4") package
- ◆ Wide 2:1 input voltage range
- ◆ Models with single-, dual- and triple output
- ◆ Models with 2 independently regulated 3.3 and 5.0 VDC outputs
- ◆ Extended operating temperature range: -40°C to +75°C
- ◆ Over temperature protection
- ◆ Under voltage lockout
- ◆ Remote On/Off
- ◆ Shielded metal case with insulated baseplate
- ◆ Optional heatsink
- ◆ Lead free design - RoHS compliant
- ◆ 3-years product warranty



The TEN 40 series is a family of high performance 40W dc-dc converter modules featuring 30 standard models with wide 2:1 input voltage ranges in a compact low profile case with industry-standard footprint. A very high efficiency allows an operating temperature range of -40°C to +75°C. Built-in filters for both input and output minimizes the need for external filtering. Further standard features include remote On/Off, output voltage trimming, over voltage protection, under voltage lockout and short circuit protection.

Typical applications for these products are battery operated equipment and distributed power architectures in communication and industrial electronics, everywhere where isolated, tightly regulated voltages are required and space is limited on the PCB.

Models

Order code	Input voltage range	Output 1	Output 2	Output 3	Efficiency typ..
TEN 40-1210	9 – 18 VDC (nominal 12 VDC)	3.3 VDC / 8.0 A	*5 VDC / 8.0 A -12 VDC / 1.8 A -15 VDC / 1.4 A	-12 VDC / 0.4 A -15 VDC / 0.3 A -12 VDC / 0.4 A -15 VDC / 0.3 A	86 %
TEN 40-1211		5 VDC / 8.0 A			86 %
TEN 40-1212		12 VDC / 3.3 A			86 %
TEN 40-1220		*3.3 VDC / 8.0 A			85 %
TEN 40-1222		+12 VDC / 1.8 A			85 %
TEN 40-1223		+15 VDC / 1.4 A			85 %
TEN 40-1233		3.3 VDC / 6.0 A			84 %
TEN 40-1234		3.3 VDC / 6.0 A			84 %
TEN 40-1231		5 VDC / 6.0 A			86 %
TEN 40-1232		5 VDC / 6.0 A			86 %
TEN 40-2410	18 – 36 VDC (nominal 24 VDC)	3.3 VDC / 8.0 A	*5 VDC / 8.0 A -12 VDC / 1.8 A -15 VDC / 1.4 A	-12 VDC / 0.4 A -15 VDC / 0.3 A -12 VDC / 0.4 A -15 VDC / 0.3 A	87 %
TEN 40-2411		5 VDC / 8.0 A			89 %
TEN 40-2412		12 VDC / 3.3 A			88 %
TEN 40-2420		*3.3 VDC / 8.0 A			86 %
TEN 40-2422		+12 VDC / 1.8 A			87 %
TEN 40-2423		+15 VDC / 1.4 A			87 %
TEN 40-2433		3.3 VDC / 6.0 A			85 %
TEN 40-2434		3.3 VDC / 6.0 A			85 %
TEN 40-2431		5 VDC / 6.0 A			87 %
TEN 40-2432		5 VDC / 6.0 A			87 %
TEN 40-4810	36 – 75 VDC (nominal 48 VDC)	3.3 VDC / 8.0 A	*5 VDC / 8.0 A -12 VDC / 1.8 A -15 VDC / 1.4 A	-12 VDC / 0.4 A -15 VDC / 0.3 A -12 VDC / 0.4 A -15 VDC / 0.3 A	88 %
TEN 40-4811		5 VDC / 8.0 A			90 %
TEN 40-4812		12 VDC / 3.3 A			89 %
TEN 40-4820		*3.3 VDC / 8.0 A			88 %
TEN 40-4822		+12 VDC / 1.8 A			87 %
TEN 40-4823		+15 VDC / 1.4 A			87 %
TEN 40-4833		3.3 VDC / 6.0 A			86 %
TEN 40-4834		3.3 VDC / 6.0 A			86 %
TEN 40-4831		5 VDC / 6.0 A			88 %
TEN 40-4832		5 VDC / 6.0 A			88 %

Note - Multi output models have a common ground.

Input Specifications

Input current at no load	12 V models: 200 mA typ. 24 V models: 100 mA typ. 48 V models: 50 mA typ.
Input current at full load (nominal input 12/24/48 Vin)	3.3 V single output models: 2680 / 1325 / 655 mA typ. 5.0 / 12 V single output models: 4065 / 2000 / 1000 mA typ. 3.3 & 5 V dual output models: 3415 / 1685 / 825 mA typ. ± 12 / ± 15 V dual output models: 4400 / 2100 / 1050 mA typ. 3.3 V triple output models: 3000 / 1500 / 750 mA typ. 5.0 V triple output models: 4000 / 1990 / 980 mA typ.
Input voltage variation (dv/dt)	5 V/ms max. (complies to ETS300 132 part 4.4)
Start-up voltage / under voltage lockout	12 Vin models: 9 VDC / 8 VDC (typ.) 24 Vin models: 17.8 VDC / 15.8 VDC (typ.) 48 Vin models: 36 VDC / 33 VDC (typ.)
Surge voltage (100 msec. max.)	12 / 24 / 48 Vin models: 25/50/100 V max.
Conducted noise (input)	EN 55022 level A, FCC part 15, level A (with external components) Please refer to Application note: www.tracopower.com/overview/ten40
ESD (input)	EN 61000-4-2, perf. criteria B
Fast transient (input)	EN 61000-4-4, perf. criteria B
Surge (input)	EN 61000-4-5, perf. criteria B

Output Specifications

Voltage set accuracy	± 1 % (± 5 % for auxiliary outputs)
Output voltage adjustment	± 10 % (only for single output models and symetric dual output models) Please refer to Application note: www.tracopower.com/overview/ten40
Regulation	– Input variation Vin min. to Vin max. - single output models: 0.5 % max. - dual output models: 1 % max. - triple output models (main/auxiliary): 1 % max. / 5 % max. – Load variation 10 – 100 % - single output models: 0.5 % max. - dual output models: 1 % max. - triple output models (main/auxiliary): 2 % max. / 5 % max. – Load cross variation 25 % / 100 % - Dual output models: 5 % max. - triple output models (main/auxiliary): 1 % max. / 5 % max.
Temperature coefficient	± 0.02 %/K max.
Ripple and noise (20 MHz Bandwidth)	3.3 V & 5 V outputs: 50 mVpk-pk max. dual outputs: 150 mVpk-pk max. all other outputs: 75 mVpk-pk max.
Start up time (nominal Vin and constant resistive load)	25 ms typ.
Transient response time (25% load change)	300 μ s typ.
Short circuit protection	indefinite (automatic recovery)
Over load protection	150 % of lout max typ. foldback
Thermal shutdown	at 115°C typ.
Over voltage protection	3.3 V output: 3.9 V 5 V output: 6.2 V 12 V output: 15 V 15 V output: 18 V

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Output Specifications

Minimum load (only for multiple output models)

10% of rated max current (on each output)
 (operation at lower load condition will not damage these converters, however, they may not meet all listed specifications)

Capacitive load output models	3.3 V / 5 V / 12 V / 15 V:	21'000 / 13'600 / 2'360 / 1510 μ F max.
	dual output models (3.3 V / 5 V):	11'000 / 6'800 μ F max.
	dual output models (± 12 V / ± 15 V):	1'200 / 750 μ F max. (on each output)
	3.3 V triple output models:	13'000 / 330 μ F max. (main-/output 2 & 3)

General Specifications

Temperature ranges	– Operating – Case temperature – Storage	–40°C to +75°C +100°C max. –55°C to +125°C
Derating		see application note: www.tracopower.com/overview/ten40
Humidity (non condensing)		95 % rel H max.
Reliability, calculated MTBF (MIL-HDBK-217F, at +25°C, ground benign)		>920'000 h
Isolation voltage (60 sec.)	– Input / Output	1'500 VDC
Isolation resistance	– Input / Output	>1'000 M Ohm
Isolation capacitance	– Input / Output	1000 pF max.
Remote On/Off	– On: – Off: – Off idle current:	3.5 ... 12 VDC or open circuit. 0 ... 1.2 VDC or short circuit pin 3 and pin 2 2.5 mA max.
Switching frequency (fixed)		300 kHz typ. (Pulse width modulation PWM)
Vibration		10–55 Hz, 10G, 30 minutes along X,Y,Z
Safety standards		UL 60950, EN 60950, IEC 60950 compliance UL 62368, EN 62368, IEC 62368 compliance up to 60 VDC input voltage (SELV limit)
Safety approvals	– Certification documents	www.tracopower.com/overview/ten40


Physical Specifications

Casing material		copper, nickel plated
Baseplate material		none conductive FR4
Potting material		epoxy (UL 94V-0 -rated)
Weight		65 g (2.3oz)
Soldering temperature		max. 265°C / 10 sec.
Environmental compliance	– Reach – RoHS	www.tracopower.com/info/reach-declaration.pdf RoHS directive 2011/65/EU

Supporting documents : www.tracopower.com/overview/ten40

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Outline Dimensions






Dimensions in [mm], () = Inch
 Pin diameter: 1.0 ± 0.05 (0.04 ± 0.002)
 Pin pitch tolerances: ± 0.35 (± 0.014)
 Case tolerances: ± 0.5 (± 0.02)

Pin-Out

Pin	Single	Dual symmetric	Dual asymmetric	Triple
1	+Vin (Vcc)	+Vin (Vcc)	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)	-Vin (GND)	-Vin (GND)
3	Remote On/Off			
4	No con.	No pin	Vout 1	Vout 2
5	-Sense*	Vout 1	Common	Common
6	+Sense*	Common	No con.	Vout 3
7	+Vout	Common	No con.	Vout 1
8	-Vout	Vout 2	Vout 2	Common
9	Trim	Trim	Common	No con.

*Sense line to be connected to the output under regard of polarity

Heat-sink TEN-HS3



Order code: TEN-HS3

(cont.: heat-sink, thermal pad, 2 clamps)

Material: Aluminum

Finish: Anodic treatment (black)

Weight: 22 g (0.78oz) (without converter)

Note:

The product label on converter has to be removed before mounting the heat-sink.

For volume orders converters will be supplied with heat-sinks already mounted. Please contact factory for quotation.

Separate heat-sinks are only available for prototypes and small quantity orders.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TRACO Power:

<u>TEN 40-2431</u>	<u>TEN 40-2412</u>	<u>TEN 40-1211</u>	<u>TEN 40-2411</u>	<u>TEN 40-2423</u>	<u>TEN 40-2410</u>	<u>TEN 40-4820</u>	<u>TEN 40-2422</u>
<u>TEN 40-4811</u>	<u>TEN 40-1212</u>	<u>TEN 40-1220</u>	<u>TEN 40-4822</u>	<u>TEN 40-4823</u>	<u>TEN 40-4834</u>	<u>TEN 40-1210</u>	<u>TEN 40-1223</u>
<u>TEN 40-1231</u>	<u>TEN 40-1233</u>	<u>TEN 40-4832</u>	<u>TEN 40-1222</u>	<u>TEN 40-4831</u>	<u>TEN 40-4833</u>	<u>TEN 40-4812</u>	<u>TEN 40-2433</u>
<u>TEN 40-2432</u>	<u>TEN 40-1232</u>	<u>TEN 40-1234</u>	<u>TEN 40-2420</u>	<u>TEN 40-4810</u>	<u>TEN 40-2434</u>		