



- (1). Inductance tested at 0.25V, 0ADC and 25°C.
Tolerance of inductance: 0.9uH-6.8uH: $\pm 30\%$ (N).
10uH-100uH: $\pm 20\%$ (M).
- (2).DCR measured at 25°C.
- (3).The DC current at which the inductance decreases by 10% from its initial value.
- (4).The DC current that results in a 40°C temperature rise from 25°C ambient.

Custom versions available upon request.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bel:

[SCNR8040-101](#) [SCNR8040-100](#) [SCNR8040-0R9](#) [SCNR8040-6R8](#) [SCNR8040-680](#) [SCNR8040-2R0](#) [SCNR8040-470](#) [SCNR8040-4R7](#) [SCNR8040-330](#) [SCNR8040-220](#) [SCNR8040-1R4](#) [SCNR8040-150](#) [SCNR8040-3R6](#)