

- Compact metal package
- Ultra wide 4:1 input voltage ranges
9–36, 18–75, 43–160 VDC
- EN 50155 approval for railway applications
- Very high efficiency up to 91%
- No minimum load
- Soft start
- Under voltage lock-out circuit
- Adjustable output voltage +10 / -20%
- Sense line



The TEP 200WIR Series is a family of isolated high performance DC/DC converter modules with ultra-wide 4:1 input voltage ranges. They come in rugged, sealed industry standard half brick package. A very high efficiency allows full power operation at 25°C with only 100 LFM air flow cooling and operation at 60°C with only 40% power derating. The very wide input voltage range and reverse input voltage protection make these converters interesting solution for battery operated systems. Typical applications are in telecom/datacom, industry control and railway systems for onboard power distribution.

Models				
Order Code	Input Voltage Range	Output Voltage nom.	Output Current max.	Efficiency typ.
TEP 200-2412WIR	9 - 36 VDC (24 VDC nom.)	12 VDC	15'000 mA	89 %
TEP 200-2413WIR		15 VDC	12'000 mA	90 %
TEP 200-2415WIR		24 VDC	7'500 mA	90 %
TEP 200-2416WIR		28 VDC	6'500 mA	90 %
TEP 200-2418WIR		48 VDC	3'700 mA	89 %
TEP 200-4812WIR	18 - 75 VDC (48 VDC nom.)	12 VDC	18'000 mA	90 %
TEP 200-4813WIR		15 VDC	14'000 mA	91 %
TEP 200-4815WIR		24 VDC	9'000 mA	90 %
TEP 200-4816WIR		28 VDC	7'500 mA	91 %
TEP 200-4818WIR		48 VDC	4'500 mA	90 %
TEP 200-7212WIR	43 - 160 VDC (110 VDC nom.)	12 VDC	20'000 mA	89 %
TEP 200-7213WIR		15 VDC	16'000 mA	90 %
TEP 200-7215WIR		24 VDC	10'000 mA	89 %
TEP 200-7216WIR		28 VDC	8'500 mA	90 %
TEP 200-7218WIR		48 VDC	5'000 mA	89 %

Options

TEP-HS1	- Optional Heat Sink: www.tracopower.com/products/tep-hs1.pdf
on demand (backorder with MOQ non stocking item)	- Optional model with 3.3 VDC / 50'000 mA Output and 9 - 36 VDC Input - Optional model with 5 VDC / 36'000 mA Output and 9 - 36 VDC Input - Optional model with 3.3 VDC / 50'000 mA Output and 18 - 75 VDC Input - Optional model with 5 VDC / 40'000 mA Output and 18 - 75 VDC Input - Optional model with 53 VDC / 3'800 mA Output and 33 - 75 VDC Input - Optional model with 3.3 VDC / 57'000 mA Output and 43 - 160 VDC Input - Optional model with 5 VDC / 44'000 mA Output and 43 - 160 VDC Input - 2:1 Input models - Negative (passive = Off) Remote On/Off function - Sync pin to synchronize switching frequency of up to 3 units (EMC reason)

Input Specifications

Input Current	- At no load	24 Vin models: 35 mA typ. 48 Vin models: 20 mA typ. 110 Vin models: 10 mA typ.
Surge Voltage		24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.) 110 Vin models: 185 VDC max. (1 s max.)
Under Voltage Lockout		24 Vin models: 7.3 VDC min. / 7.7 VDC typ. / 8.1 VDC max. 48 Vin models: 15.5 VDC min. / 16 VDC typ. / 16.3 VDC max. 110 Vin models: 33 VDC min. / 34.5 VDC typ. / 36 VDC max.
Recommended Input Fuse		24 Vin models: 32'000 mA (fast acting) 48 Vin models: 20'000 mA (fast acting) 110 Vin models: 10'000 mA (fast acting) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications

Output Voltage Adjustment		-20% to +10% (By external trim resistor) See application note: www.tracopower.com/overview/tep200wir Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax) - Load Variation (0 - 100%)	0.1% max. 0.1% max.
Ripple and Noise (20 MHz Bandwidth)		3.3 Vout models: 75 mVp-p max. (w/ 1 µF X7R // 25 µF poscap) 5 Vout models: 75 mVp-p max. (w/ 1 µF X7R // 25 µF poscap) 12 Vout models: 100 mVp-p max. (w/ 1 µF X7R // 25 µF poscap) 15 Vout models: 100 mVp-p max. (w/ 1 µF X7R // 25 µF poscap) 24 Vout models: 200 mVp-p max. (w/ 4.7 µF X7R) 28 Vout models: 200 mVp-p max. (w/ 4.7 µF X7R) 48 Vout models: 300 mVp-p max. (w/ 2.2 µF X7R)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Capacitive Load	- 24 Vin input	3.3 Vout models:	151'000 µF max.
		5 Vout models:	72'000 µF max.
		12 Vout models:	12'500 µF max.
		15 Vout models:	8'000 µF max.
		24 Vout models:	3'100 µF max.
		28 Vout models:	2'300 µF max.
	- 48 Vin input	48 Vout models:	770 µF max.
		3.3 Vout models:	151'000 µF max.
		5 Vout models:	80'000 µF max.
		12 Vout models:	15'000 µF max.
		15 Vout models:	9'300 µF max.
		24 Vout models:	3'700 µF max.
	- 110 Vin input	28 Vout models:	2'600 µF max.
		48 Vout models:	930 µF max.
		3.3 Vout models:	172'000 µF max.
		5 Vout models:	88'000 µF max.
		12 Vout models:	16'600 µF max.
		15 Vout models:	10'600 µF max.
		24 Vout models:	4'100 µF max.
		28 Vout models:	3'000 µF max.
	48 Vout models:		1'000 µF max.
Minimum Load		Not required	
Temperature Coefficient		±0.02 %/K max.	
Start-up Time		75 ms typ.	
Short Circuit Protection		Continuous, Automatic recovery	
Output Current Limitation		120 - 150% of Iout max.	
Overvoltage Protection		115 - 130% of Vout nom.	
Transient Response		- Response Time	
		200 µs typ. / 250 µs max. (25% Load Step)	

Safety Specifications

Safety Standards	- IT / Multimedia Equipment	EN 60950-1
		EN 62368-1
		IEC 60950-1
		IEC 62368-1
		UL 60950-1
		UL 62368-1
	- Railway Applications	EN 50155
	- Certification Documents	www.tracopower.com/overview/tep200wir
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI Emissions	- Conducted Emissions	EN 55011 class B (with external filter)
		EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55011 class B (with external filter)
		EN 55032 class B (with external filter)
		External filter proposal: www.tracopower.com/overview/tep200wir

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

EMS Immunity	- Electrostatic Discharge	Air: EN 50155 (Railway Applications) EN 50121-3-2 (EMC for Rolling Stock)
	- RF Electromagnetic Field	Contact: EN 61000-4-2, ± 8 kV, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-2, ± 6 kV, perf. criteria A
	- Conducted RF Disturbances	EN 61000-4-3, 20 V/m, perf. criteria A
	- PF Magnetic Field	EN 61000-4-4, ± 2 kV, perf. criteria A
		Ext. input component: EN 61000-4-5, ± 2 kV, perf. criteria A
		24 & 48 Vin models: 2 x KY 20 μ F
		110 Vin models: 2 x KXJ 150 μ F
		Continuous: EN 61000-4-6, 10 Vrms, perf. criteria A
		1 s: EN 61000-4-8, 100 A/m, perf. criteria A
		EN 61000-4-8, 1000 A/m, perf. criteria A

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +75°C
	- Case Temperature	+105°C max.
	- Storage Temperature	-55°C to +125°C
Power Derating	- High Temperature	See application note: www.tracopower.com/overview/tep200wir
Over Temperature Protection Switch Off	- Protection Mode	115°C typ. (Automatic recovery at 105°C typ.)
	- Measurement Point	Base-Plate
Cooling System		Natural convection (20 LFM)
Sense Function		10% max. of Vout nom. (Sense line to be connected to the output either at the module or at the load under regard of polarity.)
Remote Control	- Voltage Controlled Remote	On: 3.0 to 12 VDC or open circuit Off: 0 to 1.2 VDC or short circuit Refers to 'Remote' and '-Vin' Pin
	- Off Idle Input Current	3 mA typ.
	- Remote Pin Input Current	-0.5 to 1.0 mA
Altitude During Operation		2'000 m max. (for reinforced insulation) 5'000 m max. (for functional insulation))
Switching Frequency		225 - 275 kHz (PWM) 250 kHz typ. (PWM)
Insulation System		Reinforced Insulation (110 Vin models only) Functional Insulation (other models)
Working Voltage (rated)		145 VAC (3.3 and 5 Vout models) 185 VAC (48 and 53 Vout models) 172 VAC (other output models)
Isolation Test Voltage	- Input to Output, 60 s	3'000 VAC (110 Vin models) 3'000 VDC (other models)
	- Input to Case, 60 s	1'500 VAC (110 Vin models) 1'600 VDC (other models)
	- Output to Case, 60 s	1'500 VAC (110 Vin models) 1'600 VDC (other models)
Isolation Resistance	- Input to Output, 500 VDC	1'000 M Ω min.
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	2'500 pF max.
Reliability	- Calculated MTBF	300'000 h (MIL-HDBK-217F, ground benign)
Environment	- Vibration	MIL-STD-810F EN 61373
	- Mechanical Shock	MIL-STD-810F EN 61373
	- Thermal Shock	MIL-STD-810F EN 50155

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Housing Material	Alu base-plate w. metal case (24 and 48 Vin models) Alu base-plate w. plastic case (110 Vin models)
Base Material	Non-conductive FR4 (UL 94 V-0 rated) (24 and 48 Vin models only)
Potting Material	Silicone (UL 94 V-0 rated)
Pin Material	Copper
Pin Foundation Plating	Nickel (2 - 3 µm)
Pin Surface Plating	Tin (3 - 5 µm), matte
Housing Type	Metal Case (24 and 48 Vin models) Plastic Case (110 Vin models)
Mounting Type	PCB Mount
Connection Type	THD (Through-Hole Device)
Footprint Type	Half-Brick
Weight	105 g
Thermal Impedance	6.1 K/W 4.6 K/W (with Heat Sink)
Environmental Compliance	- REACH Declaration www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant - RoHS Declaration www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule). The SCIP number is provided on request.) - Flammability (EN 45545-2) www.tracopower.com/info/en45545-declaration.pdf


Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tep200wir

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Dimensions in mm (inch)
 Tolerances ± 0.5 (± 0.02)
 Pin pitch tolerances ± 0.25 (± 0.01)
 Mounting hole pitch tolerances
 ± 0.25 (± 0.01)

Pin diameter pins 5 & 9: 2.0 (0.08)
 Pin diameter other pins: 1.0 (0.04)

Pinout

Pin	Function
1	-Vin (GND)
2	NC
3	Remote
4	+Vin (Vcc)
5	-Vout
6	-Sense
7	Trim
8	+Sense
9	+Vout
10	Sync (on demand)

NC: No Connection

The screw 1 locked torque
 (24 and 48Vout models):
 MAX 5.0kgf-cm/0.49N-m

The screw 1 locked torque
 (110Vout models):
 MAX 3.5kgf-cm/0.34N-m

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TRACO Power:

[TEP 200-2411WIRCMF](#) [TEP 200-4810WIR](#) [TEP 200-4810WIRCMF](#) [TEP 200-7211WIR](#) [TEP 200-2411WIR](#) [TEP](#)
[200-4811WIRCM](#) [TEP 200-2410WIRCMF](#) [TEP 200-7210WIRCMF](#) [TEP 200-7211WIRCMF](#) [TEP 200-2410WIR](#) [TEP](#)
[200-7210WIRCM](#) [TEP 200-7211WIRCM](#) [TEP 200-2410WIRCM](#) [TEP 200-4810WIRCM](#) [TEP 200-4811WIRCMF](#) [TEP](#)
[200-7210WIR](#) [TEP 200-4811WIR](#) [TEP 200-2411WIRCM](#) [TEP 200-2412WIR](#) [TEP 200-2412WIRCM](#) [TEP 200-](#)
[2413WIR](#) [TEP 200-2413WIRCM](#) [TEP 200-2415WIR](#) [TEP 200-2415WIRCM](#) [TEP 200-7215WIRCM](#) [TEP 200-](#)
[7216WIR](#) [TEP 200-7216WIRCM](#) [TEP 200-7218WIR](#) [TEP 200-7218WIRCM](#) [TEP 200-2416WIRCM](#) [TEP 200-](#)
[4818WIRCM](#) [TEP 200-7212WIR](#) [TEP 200-7212WIRCM](#) [TEP 200-7213WIR](#) [TEP 200-7213WIRCM](#) [TEP 200-](#)
[7215WIR](#) [TEP 200-4813WIRCM](#) [TEP 200-4815WIR](#) [TEP 200-4815WIRCM](#) [TEP 200-4816WIR](#) [TEP 200-](#)
[4816WIRCM](#) [TEP 200-4818WIR](#) [TEP 200-2416WIR](#) [TEP 200-2418WIR](#) [TEP 200-2418WIRCM](#) [TEP 200-4812WIR](#)
[TEP 200-4812WIRCM](#) [TEP 200-4813WIR](#)