

- Encapsulated in 1"x1" metal package
- EN 50155 and EN 61373 certified
- Wide 4:1 input voltage range:
9-36, 18-75, 36-160 VDC
- -40°C up to +65°C without derating
- Up to 92% efficiency
- Up to 3000 VDC I/O-isolation
- EN 45545-2 fire behavior
- Remote on/off and trim function
- Undervoltage lockout (UVLO),
short-circuit protection (SCP),
overvoltage protection (OVP) and
overtemperature protection (OTP)
- 3-year product warranty



The THN 30WIR is a series of DC/DC converters designed for highest reliability in harsh environments. With an output power of 30 Watts, this series expands our portfolio of EN 50155 railway certified wide input voltage range 1"x1" DC/DC converters. The THN 30WIR is shielded by a metal enclosure on all six sides for lowest susceptibility to electromagnetic interference. Its full encapsulation guarantees highest resistance to thermal shocks as well as mechanical shocks and vibration. Thanks to its power conversion efficiency of up to 92%, the THN 30WIR can operate at ambient temperatures between -40°C and +65°C without derating and without the need for additional cooling (depending on the model). The THN 30WIR is EN 61373 certified for mechanical shock and vibration and EN 45545-2 certified for fire behavior. It comes with IEC/EN/UL 62368-1 safety approvals.

Models						
Order Code	Input Voltage Range	Output 1		Output 2		Efficiency typ.
		Vnom	I _{max}	Vnom	I _{max}	
THN 30-2410WIR	9 - 36 VDC (24 VDC nom.)	3.3 VDC	7'000 mA			88 %
THN 30-2411WIR		5.1 VDC	6'000 mA			89 %
THN 30-2412WIR		12 VDC	2'500 mA			89 %
THN 30-2413WIR		15 VDC	2'000 mA			89 %
THN 30-2415WIR		24 VDC	1'250 mA			90 %
THN 30-2422WIR		+12 VDC	1'250 mA	-12 VDC	1'250 mA	89 %
THN 30-2423WIR		+15 VDC	1'000 mA	-15 VDC	1'000 mA	91 %
THN 30-2425WIR		+24 VDC	625 mA	-24 VDC	625 mA	91 %
THN 30-4810WIR	18 - 75 VDC (48 VDC nom.)	3.3 VDC	7'000 mA			88 %
THN 30-4811WIR		5.1 VDC	6'000 mA			90 %
THN 30-4812WIR		12 VDC	2'500 mA			90 %
THN 30-4813WIR		15 VDC	2'000 mA			91 %
THN 30-4815WIR		24 VDC	1'250 mA			92 %
THN 30-4822WIR		+12 VDC	1'250 mA	-12 VDC	1'250 mA	91 %
THN 30-4823WIR		+15 VDC	1'000 mA	-15 VDC	1'000 mA	91 %
THN 30-4825WIR		+24 VDC	625 mA	-24 VDC	625 mA	92 %
THN 30-7210WIR	36 - 160 VDC (110 VDC nom.)	3.3 VDC	7'000 mA			88 %
THN 30-7211WIR		5.1 VDC	6'000 mA			90 %
THN 30-7212WIR		12 VDC	2'500 mA			90 %
THN 30-7213WIR		15 VDC	2'000 mA			90 %
THN 30-7215WIR		24 VDC	1'250 mA			91 %
THN 30-7222WIR		+12 VDC	1'250 mA	-12 VDC	1'250 mA	90 %
THN 30-7223WIR		+15 VDC	1'000 mA	-15 VDC	1'000 mA	90 %
THN 30-7225WIR		+24 VDC	625 mA	-24 VDC	625 mA	91 %

Options

THN-HS2	- Optional Heat Sink: www.tracopower.com/overview/thn-hs2
on demand (backorder with MOQ non stocking item)	- Optional Heat Sink: www.tracopower.com/overview/thn-hs3 - Optional Heat Sink: www.tracopower.com/overview/thn-hs4 - Optional model with 5 VDC and 6'000 mA Output, and 9 - 36 VDC Input - Optional model with 54 VDC and 556 mA Output, and 9 - 36 VDC Input - Optional model with 5 VDC and 6'000 mA Output, and 18 - 75 VDC Input - Optional model with 54 VDC and 556 mA Output, and 18 - 75 VDC Input - Optional model with 5 VDC and 6'000 mA Output, and 36 - 160 VDC Input - Optional model with 54 VDC and 556 mA Output, and 36 - 160 VDC Input

Input Specifications

Input Current	- At no load	110 Vin models: 7 mA typ. 24 Vin models: 10 mA typ. (3.3 Vout model) 10 mA typ. (5 Vout model) 10 mA typ. (5.1 Vout model) 10 mA typ. (12 Vout model) 10 mA typ. (15 Vout model) 10 mA typ. (24 Vout model) 14 mA typ. (54 Vout model) 10 mA typ. (12 / -12 Vout model) 10 mA typ. (15 / -15 Vout model) 12 mA typ. (24 / -24 Vout model) 48 Vin models: 10 mA typ. (3.3 Vout model) 10 mA typ. (5 Vout model) 10 mA typ. (5.1 Vout model) 8 mA typ. (12 Vout model) 8 mA typ. (15 Vout model) 8 mA typ. (24 Vout model) 12 mA typ. (54 Vout model) 8 mA typ. (12 / -12 Vout model) 8 mA typ. (15 / -15 Vout model) 7 mA typ. (24 / -24 Vout model)
Surge Voltage		24 Vin models: 50 VDC max. (1 s max.) 48 Vin models: 100 VDC max. (1 s max.) 110 Vin models: 185 VDC max. (1 s max.)
Under Voltage Lockout		24 Vin models: 7.5 VDC min. / 8 VDC typ. / 8.8 VDC max. 48 Vin models: 15.5 VDC min. / 16 VDC typ. / 17.5 VDC max. 110 Vin models: 32 VDC min. / 34 VDC typ. / 35.5 VDC max.
Recommended Input Fuse		24 Vin models: 6'000 mA (slow blow) 48 Vin models: 3'000 mA (slow blow) 110 Vin models: 1'500 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)
Input Filter		Internal Pi-Type

Output Specifications

Output Voltage Adjustment	-10% to +20% (15 & 24 Vout models) -20 to +6% (54 Vout models) ±10% (other models) (single output models only) (By external trim resistor) See application note: www.tracopower.com/overview/thn30wir Output power must not exceed rated power!
Voltage Set Accuracy	±1% max.

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Regulation	- Input Variation (Vmin - Vmax)	single output models: 0.2% max. dual output models: 0.5% max.
	- Load Variation (0 - 100%)	single output models: 0.2% max. dual output models: 1% max. (Output 1) 1% max. (Output 2)
	- Voltage Balance (symmetrical load)	dual output models: 2% max.
	- Cross Regulation (25% / 100% asym. load)	dual output models: 5% max.
Ripple and Noise (20 MHz Bandwidth)	- single output	3.3 Vout models: 75 mVp-p typ. (w/ 22 µF)
		5 Vout models: 75 mVp-p typ. (w/ 22 µF)
		5.1 Vout models: 75 mVp-p typ. (w/ 22 µF)
		12 Vout models: 100 mVp-p typ. (w/ 22 µF 22 µF)
		15 Vout models: 100 mVp-p typ. (w/ 22 µF 22 µF)
		24 Vout models: 100 mVp-p typ. (w/ 6.8 µF 6.8 µF)
	- dual output	54 Vout models: 125 mVp-p typ. (w/ 2.2 µF 2.2 µF)
		12 / -12 Vout models: 100 / 100 mVp-p typ. (w/ 10 µF)
		15 / -15 Vout models: 100 / 100 mVp-p typ. (w/ 10 µF)
		24 / -24 Vout models: 100 / 100 mVp-p typ. (w/ 4.7 µF)
Capacitive Load	- single output	3.3 Vout models: 10'000 µF max.
		5 Vout models: 7'200 µF max.
		5.1 Vout models: 7'200 µF max.
		12 Vout models: 1'200 µF max.
		15 Vout models: 1'000 µF max.
		24 Vout models: 375 µF max.
	- dual output	54 Vout models: 75 µF max.
		12 / -12 Vout models: 750 / 750 µF max.
		15 / -15 Vout models: 500 / 500 µF max.
		24 / -24 Vout models: 180 / 180 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Hold-up Time		10 ms min. (acc. to EN 50155 Class S2, see application note for ext. capacitor calculation: www.tracopower.com/info/holdup_en50155.pdf)
Start-up Time		30 ms typ. / 40 ms max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		210% max. of Iout max. 170% typ. of Iout max.
Overvoltage Protection		133% typ. of Vout nom. (depending on model) 3.7 VDC typ. / 5.4 VDC max. (3.3 Vo models) 6.3 VDC typ. / 7.4 VDC max. (5 Vo models) 6.3 VDC typ. / 7.4 VDC max. (5.1 Vo models) 13.5 VDC typ. / 19.6 VDC max. (12 Vo models) 18.3 VDC typ. / 22.0 VDC max. (15 Vo models) 29.1 VDC typ. / 32.5 VDC max. (24 Vo models) 58.5 VDC typ. / 65.5 VDC max. (54 Vo models) 13.5 VDC typ. / 19.6 VDC max. (±12 Vo models) 18.3 VDC typ. / 22.0 VDC max. (±15 Vo models) 29.1 VDC typ. / 32.5 VDC max. (±24 Vo models)
Transient Response	- Response Time	250 µs typ. (25% Load Step)

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1 EN 50155 www.tracopower.com/overview/thn30wir
	- Railway Applications	
	- Certification Documents	
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 50121-3-2 (EMC for Rolling Stock) EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	- Radiated Emissions	EN 55032 class A (with external filter) EN 55032 class B (with external filter)
	External filter proposal:	www.tracopower.com/overview/thn30wir
EMS (Immunity)		EN 50121-3-2 (EMC for Rolling Stock) EN 55024 (IT Equipment) EN 55035 (Multimedia)
	- Electrostatic Discharge	Air: EN 61000-4-2, ± 8 kV, perf. criteria A Contact: EN 61000-4-2, ± 6 kV, perf. criteria A
	- RF Electromagnetic Field	EN 61000-4-3, 20 V/m, perf. criteria A
	- EFT (Burst) / Surge	EN 61000-4-4, ± 2 kV, perf. criteria A EN 61000-4-5, ± 2 kV, perf. criteria A
	Ext. input component:	24 Vin / 54 Vout model: 470 μ F / 50 V + TVS diode SMBJ58A 24 & 48 Vin models: 220 μ F / 110 V, KY series 110 Vin models: 150 μ F / 200 V 150 μ F / 200 V, KXJ series + TVS diode SMBJ220A
	- Conducted RF Disturbances	EN 61000-4-6, 10 Vrms, perf. criteria A
	- PF Magnetic Field	Continuous: EN 61000-4-8, 100 A/m, perf. criteria A 1 s: EN 61000-4-8, 1000 A/m, perf. criteria A
EMC / Environmental	- Certification Documents	www.tracopower.com/overview/thn30wir

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +80°C -40°C to +85°C (with Heat Sink)
	- Case Temperature	+105°C max.
	- Storage Temperature	-55°C to +125°C
Power Derating	- High Temperature	Depending on model
	See application note:	www.tracopower.com/overview/thn30wir
Over Temperature Protection Switch Off	- Protection Mode	115°C typ. (Automatic recovery)
	- Measurement Point	Case
Cooling System		Natural convection (20 LFM)
Remote Control	- Voltage Controlled Remote (passive = on)	On: 3.0 to 15 VDC or open circuit Off: 0 to 1.2 VDC or short circuit Refers to 'Remote' and '-Vin' Pin
	- Off Idle Input Current	2.5 mA typ.
	- Remote Pin Input Current	-0.5 to 1.0 mA
Altitude During Operation		5'000 m max.
Regulator Topology		Flyback Converter

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Switching Frequency		210 - 370 kHz (PWM) (depending on model) 230 kHz min. / 270 kHz typ. / 310 kHz max. (24 & 48 Vin, 3.3 & 5 & 5.1 Vout models) 290 kHz min. / 330 kHz typ. / 370 kHz max. (24 & 48 Vin, other models) 210 kHz min. / 240 kHz typ. / 270 kHz max. (110 Vin, 3.3 & 5 & 5.1 Vout models) 270 kHz min. / 300 kHz typ. / 330 kHz max. (110 Vin, other models)
Insulation System		Functional Insulation
Isolation Test Voltage	- Input to Output, 60 s	2'250 VDC (24 & 48 Vin models)
	- Input to Case, 60 s	3'000 VDC (110 Vin models)
	- Output to Case, 60 s	1'600 VDC (24 & 48 Vin models)
		2'250 VDC (110 Vin models)
Creepage	- Input to Output	1'600 VDC (24 & 48 Vin models)
Clearance	- Input to Output	2'250 VDC (110 Vin models)
Isolation Resistance	- Input to Output, 500 VDC	1'600 VDC (24 & 48 Vin models)
Isolation Capacitance	- Input to Output, 100 kHz, 1 V	2'250 VDC (110 Vin models)
Reliability	- Calculated MTBF	1'000 MΩ min.
Washing Process		2'000 pF max.
Environment		1'259'000 h (MIL-HDBK-217F, ground benign)
Environment	- Vibration	According to Cleaning Guideline
	- Mechanical Shock	www.tracopower.com/info/cleaning.pdf
	- Thermal Shock	MIL-STD-810F
	- Flammability	EN 61373
		7.6 g, 3 axis, 60 min, 20-2000 Hz
Housing Material		MIL-STD-810F
Base Material		EN 61373
Isolation Frame Material		50 g, 3 axis, 11 ms
Potting Material		MIL-STD-810F
Pin Material		-55°C to +125°C, 72 cycles, 30 min each
Pin Foundation Plating		EN 45545-2
Pin Surface Plating		www.tracopower.com/info/en45545-declaration.pdf
Housing Type		Copper
Mounting Type		Non-conductive FR4 (UL 94 V-0 rated)
Connection Type		Non-conductive Plastic (UL 94 V-0 rated)
Footprint Type		Silicone (UL 94 V-0 rated)
Soldering Profile		Tinned Copper
Weight		Nickel (2 - 3 µm)
Thermal Impedance	- Case to Ambient	Tin (3 - 5 µm), matte
		Metal Case
		PCB Mount
		THD (Through-Hole Device)
		1" x 1"
		Lead-Free Wave Soldering
		260°C / 6 s max.
		18 g
		15 K/W typ. (without heatsink)
		11.1 K/W typ. (with heatsink THN-HS2)
		9.6 K/W typ. (with heatsink THN-HS3)
		8.2 K/W typ. (with heatsink THN-HS4)



All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Environmental Compliance	- REACH Declaration	www.tracopower.com/info/reach-declaration.pdf REACH SVHC list compliant REACH Annex XVII compliant www.tracopower.com/info/rohs-declaration.pdf Exemptions: 7a, 7c-I (RoHS exemptions refer to the component concentration only, not to the overall concentration in the product (O5A rule).) 29c7d85e-3517-411b-9e61-7f2681dc8c48
	- RoHS Declaration	
	- SCIP Reference Number	

Supporting Documents		
Overview Link	(for additional Documents)	www.tracopower.com/overview/thn30wir

All specifications valid at nominal voltage, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



All dimensions in mm (inch)
Tolerance: X.X ±0.5 (X.XX ±0.02)
X.XX ±0.025 (X.XXX ±0.010)
Pin dimension tolerance: ±0.10 (±0.004)

Pinout		
Pin	Single	Dual
1	+Vin	+Vin
2	-Vin	-Vin
3	Remote On/Off	Remote On/Off
4	+Vout	+Vout
5	Trim	Common
6	-Vout	-Vout

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TRACO Power:](#)

<u>THN 30-2412WIR</u>	<u>THN 30-2413WIR</u>	<u>THN 30-2415WIR</u>	<u>THN 30-2422WIR</u>	<u>THN 30-2423WIR</u>	<u>THN 30-2425WIR</u>
<u>THN 30-7215WIR</u>	<u>THN 30-7222WIR</u>	<u>THN 30-7223WIR</u>	<u>THN 30-7225WIR</u>	<u>THN 30-2410WIR</u>	<u>THN 30-2411WIR</u>
<u>THN 30-4823WIR</u>	<u>THN 30-4825WIR</u>	<u>THN 30-7210WIR</u>	<u>THN 30-7211WIR</u>	<u>THN 30-7212WIR</u>	<u>THN 30-7213WIR</u>
<u>THN 30-4810WIR</u>	<u>THN 30-4811WIR</u>	<u>THN 30-4812WIR</u>	<u>THN 30-4813WIR</u>	<u>THN 30-4815WIR</u>	<u>THN 30-4822WIR</u>