

LDD240-WU

240 W DC-DC DIN Rail Converter with Programmable Output

This LDD240-WU DC-DC converter is the optimal response to the applications where compactness and high reliability are requested.

It is isolated and offers a wide range of input and output voltages.

Simple but elegant look and ease of installation makes it ideal for various industrial applications.



FEATURES

- Output power up to 240 W (voltage dependent)
- Converts any voltage between 11 V and 55 V to any voltage between 5 V and 55 V
- Efficiency up to 92% (voltage dependent)
- Operating ambient temperature range -40°C to +70°C
- Constant current or hiccup mode limitation (user settable)
- Digital power regulation
- Isolated topology (2.2 kVDC)
- Modbus over USB interface for control and monitoring
- Multiple integrated protections
- Parallelable for power or redundancy (integrated ORing circuitry)
- Compact size in aluminum enclosure
- Dimensions: 40 x 115 x 110 mm



APPLICATIONS

- Industrial machine control
- Process control
- Energy management
- Remote control systems
- Railway applications

1. MODEL SELECTION

MODEL	INPUT VOLTAGE RANGE	INPUT CURRENT	OUTPUT VOLTAGE	MAX OUTPUT CURRENT	EFFICIENCY ¹	MAX OUTPUT POWER
LDD240-WU	11 - 55 VDC	12 A	5 - 55 VDC	10 A	77 - 92 %	240 W

¹ Depending on Vin/Vout

2. INPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	SPECIFICATION
DC Input Voltage	Nominal Range (UL certified)	12 - 48 VDC 11 - 55 VDC
DC Input Current		12 A
Recommended External Protection	Use DC rated devices	Fuse 20 A or MCB 20 A C curve

3. OUTPUT SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	SPECIFICATION
Output Voltage (Adjustable)		5 - 55 VDC
Output Current (Continuous)	240 W, See <i>Figure 1</i> .	10 A
Load Regulation	@ 5 VDC @ 12 VDC @ ≥ 24 VDC	≤ 4.0 % ≤ 2.0 % ≤ 1.5 %
Ripple & Noise ²		≤ 200 mVpp
Hold-up Time		≥ 5 ms
Parallel Connection ³	Possible for power or redundancy with integrated ORing circuitry	

² Ripple and Noise are measured with 20 MHz bandwidth, probe terminated with a 0.1 μ F MKP parallel capacitor.

³ Pay attention, set the operating mode to "parallel" when connecting more units in parallel, see Instruction Manual for details.

4. PROTECTIONS

PARAMETER	DESCRIPTION / CONDITIONS	SPECIFICATION
Input Over Voltage Protection	Active shutdown	> 60 V
Reverse Polarity Protection		
Fuse Protection	Mini ATO blade (not user replaceable)	20 A
Short Circuit Protection ⁴	Constant current or Hiccup mode, Short circuit peak current	18 A
Output Overload Protection ⁴	Constant current mode, Overload Limit, 264 W, See <i>Figure 1</i> . Hiccup mode, Overload Limit (max. 5 s), 360 W, See <i>Figure 1</i> .	11 A 15 A
Thermal Protection		
Output Over Voltage Protection	120% of Vout active self tracking	

⁴ User settable




Figure 1. Voltage derating curves

5. USER INTERFACE, SIGNALLING & CONTROL

PARAMETER	DESCRIPTION / CONDITIONS
User Interface	7 segment, 2 digit display 3 programming keys DC OK - dry contact (NO, 24 VDC / 1 A) Modbus over USB interface
Measurement Precision	Output voltage: range: 5 - 55 V $\pm 1\%$ ± 1 digit Output current: range: 0 - 16 A $\pm 3\%$ ± 1 digit Input voltage: range: 10 - 52 V $\pm 3\%$ ± 1 digit

6. ENVIRONMENTAL, EMC & SAFETY SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	SPECIFICATION
Operating Temperature	UL certified up to 60°C Start-up type tested: - 40°C, possible at Vnom with load deration.	-40 to +70 °C
Storage Temperature		-40 to +80 °C
Derating	Over 60°C, depending on Vin/Vout, see <i>Figure 2</i>	
Dissipated Power	Depending on Vin/Vout	< 28 W
Humidity	Non-condescending	5 - 95 % RH
Life Time Expectancy	Ta = 25°C, full load	180 542 (20.61) hrs (years)
MTBF	MIL-HDBK-217F at Ta = 25°C, full load	> 600 000 hrs
Overvoltage Category	EN 50178	I
Pollution Degree	IEC 60664-1	2
Protection Class	Class I	
Isolation	Input to Output Input to Ground Output to Ground	2.2 kVDC 2.2 kVDC 0.75 kVDC
Safety Standards & Approvals	UL 508 (certified) IEC/EN 61010-1 IEC/EN 61010-2-201 IEC/EN 60950	
EMC Emissions	EN 61000-6-3	
EMC Immunity	EN 61000-6-2	
Protection Degree	EN 60529	IP20
Vibration Sinusoidal	IEC 60068-2-6	5 - 17.8 Hz: ± 1.6 mm; 17.8 - 500 Hz: 2 g, 2 hours / axis (X, Y, Z)
Shock	IEC 60068-2-27	30 g 6 ms, 20 g 11 ms; 3 bumps / direction, 18 bumps total




Figure 2. Temperature derating curves

7. MECHANICAL SPECIFICATIONS

PARAMETER	DESCRIPTION / CONDITIONS	SPECIFICATION
Dimensions		40 x 115 x 110 mm 1.57 x 4.53 x 4.33 in
Weight		400 g
Mounting Rail	IEC 60715/H15/TH35-7.5(-15)	
IN/OUT Connection Terminals	Screw type pluggable (24 - 12 AWG)	2.5 mm ²
Communication Interface Connector	Mini USB-B Type (virtual Com Port)	
Case Material	Aluminum	

8. PIN LAYOUT & DESCRIPTION



CONNECTION	DESCRIPTION
INPUT CONNECTION	+ = Positive DC - = Negative DC ⊕ = Earth ground
OUTPUT CONNECTION	+ = Positive DC - = Negative DC
SIGNALLING	DC OK: dry contact • NO • COM
MINI USB TYPE	• 1 = VBUS (+5V) • 2 = Data (D-) • 3 = Data (D+) • 4 = Not connected (ID) • 5 = GND

- IDD+D- +

MECHANICAL DRAWING




Figure 3. Mechanical Drawing

Notes:

Technical parameters are typical, measured in laboratory environment at 25°C and 24 VDC Vin/Vout, at nominal values, after min. 5 minutes of operation. Power rating, losses, efficiency, ripple, thermal behaviour and start-up may change outside of the nominal rated input range. Contact factory for details.

NUCLEAR AND MEDICAL APPLICATIONS - Products are not designed or intended for use as critical components in life support systems, equipment used in hazardous environments, or nuclear control systems.

TECHNICAL REVISIONS - The appearance of products, including safety agency certifications pictured on labels, may change depending on the date manufactured. Specifications are subject to change without notice.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Bel Power Solutions:](#)

[LDD240-WU](#)