


- NOTES:
- 1.0 SPECIFICATIONS:
- 1.1 FREQUENCY RANGE: 2.0 to 8.0 GHz
 - 1.2 INSERTION LOSS: 1.0dB MAX. WHEN REFERENCED TO 6dB POWER DIVISION.
 - 1.3 AMPLITUDE UNBALANCE: 0.5dB MAX.
 - 1.4 PHASE BALANCE: 10° MAX.
 - 1.5 VSWR: 1.50:1 MAX.
 - 1.6 ISOLATION: 18dB MIN.
 - 1.7 INPUT POWER: 30 WATTS MAX.

2.0 FINISH:

GREY OVER MIL-E-15090 TYPE II, CLASS 2
OVER MIL-C-5541 CLASS 3A
MEETS MIL-F-14072
MEETS MIL-E-5400

- 3.0 MARKING:
MARK UNIT AS SHOWN
- 4.0 DIMENSIONS IN PARENTHESIS ARE
IN MILLIMETERS



MODEL NUMBER	REV.
PWD-5522-04-NNN-79	-1

REV.	DESCRIPTION	DATE
-	RELEASED	8/12/94
-1	ADDED TITLEBLOCK	7/19/05

UNLESS OTHERWISE NOTED DIMENSIONS ARE IN INCHES AND TOLERANCES ARE: 3 PLACE DECIMALS ±.005 2 PLACE DECIMALS ±.02 FRACTIONS ±1/64 PARALLELITY: T.I.R. _____ FLATNESS: T.I.R. _____ CONCENTRICITY: T.I.R. _____ ANGLES AND PERPENDICULARITY: ±1°		FSCM NO. 34078	MIDWEST MICROWAVE	
		NOTICE: The information contained in this drawing is proprietary and must not be used without the permission of Midwest Microwave		TITLE POWER DIVIDER TYPE N (4-WAY)
DRAWN/DATE A.BEATTY 8/9/94		ENG./DATE J.O'NEIL 8/10/94		DRAWING NUMBER PWD-5522-04-NNN-79
CHECKED/DATE		APPROVED/DATE		SCALE: 1=1 SHEET 1 of 1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PWD-5522-04-NNN-79](#)