

CONNECTOR P1 DESCRIPTION/ PART NO	CONNECTOR P2 DESCRIPTION/ PART NO	CABLE GROUPS: WRENCH CRIMP, (TODL CRIMP)									CKT CODE
		1(011)	2(013A)	2(013/013B)	3(012)	1(011)	2(013)	1(012)	2(011)		
		TCC-50-2	TCC-75-2	RG62	M17/167-00001 (RG623)	RG58 BLACK	RG59 BLACK	RG142	RG303		
11-01 DASH NUMBERS											
(PL1C-) 1-0453-	(PL1C-) 1-0453-	-1	-3	-4	-2	-88	-189	-203	-228	K1	
(PL1WC-) 1-0453-W	(PL1WC-) 1-0453-W	-5	-7	-8	-6	-89	-204	-205	-206	K1	
(PL1C-) 1-0453-	(PL71-1 FIS) 305-0562-1	-9	—	—	—	-90	—	-207	—	E2	
(PL1C-) 1-0453-	(PL71-2 FIS) 305-0562-3	—	-10	-11	—	—	-208	—	—	E2	
(PL1WC-) 1-0453-W	(PL71-1 FIS) 305-0562-1	-12	—	—	—	-91	—	-209	—	E2	
(PL1WC-) 1-0453-W	(PL71-2 FIS) 305-0562-3	—	-13	-14	—	—	-236	—	—	E2	
(PL20-) 1-0369-	(PL1C-) 1-0453-	-15	-17	-18	-16	-92	-238	-239	-240	K1	
(PL20-) 1-0369-	(PL1WC-) 1-0453-W	-19	-22	-23	-20	-93	-241	-242	-243	K1	
(PL3C-) 1-0045-	(PL3C-) 1-0045-	-244	-245	-246	-21	-247	-248	-249	-250	K1	
(PL20-) 1-0369-	(PL20-) 1-0369-	-24	-26	-27	-25	-251	-190	-252	-253	K1	
(PL20-) 1-0369-	(PL40-) 1-0014-	-28	-254	-255	-29	-94	-256	-257	-258	K1	
(CJ20-) 1-0134-	(CJ40-) 1-0135-	-30	-259	-260	-31	-95	-261	-262	-263	K1	
(PL40-) 1-0014-	(CJ40-) 1-0135-	-32	-33	-34	-264	-96	-265	-266	-267	K1	
(PL95-) 1-0370-	(PL95-) 1-0370-	-35	-77	-268	-195	-97	-269	-270	-271	K1	
(PL95-) 1-0370-	(PL1C-) 1-0453-	-36	-272	-273	-274	-98	-275	-276	-277	K1	
(PL1WC-) 1-0453-W	(J3WE) 1-0378-W	-278	-37	-279	-280	-281	-282	-283	—	K1	
UG111/U	UG111/U	—	-38	—	—	—	—	—	—	K1	
(PL20-) 1-0369-	(CJ20-) 1-0134-	-62	-63	-64	-39	-106	-284	-285	-286	K1	
(BJ26-) 1-0341-	(PL40-) 1-0014-	-40	-287	-288	-289	-99	-290	-291	-292	K1	
(PL11C-) 1-0326-	(PL11C-) 1-0326-	-293	-82	-41	-294	-295	-296	-297	-298	K1	
(PL94-) 1-0029-	(PL20-) 1-0369-	-42	-299	-300	-301	-100	-302	-303	-304	K1	
(PL123-) 1-0390-	(PL1C-) 1-0453-	-43	-44	-45	-305	-101	-306	-307	-308	K1	
(UPL123-) 1-0390-U	(PL1WC-) 1-0453-W	-46	-47	-48	-309	-102	-310	-311	-312	K1	
(MP2W) 1-0398	(PL1WC-) 1-0453-W	—	-49	-313	—	—	-314	—	—	K1	
(CJ40-) 1-0135-	(PL60-) 1-0353-	-50	—	—	-315	-103	—	-316	-317	K1	
(PL20-) 1-0369-	(PL50-) 1-0016-	-170	-172	-51	-231	-318	-319	-320	—	K1	
(PL20-) 1-0369-	(BANANA PLUG) 210-103	-52	—	—	—	-104	—	—	—	X1	
(PL20-) 1-0369-	(BANANA PLUG) 210-102	—	-53	—	—	—	—	—	—	X1	
(J12-) 1-0258-	(PL1WC-) 1-0453-W	-321	-54	-322	-323	-324	-325	-326	—	K1	
(PL11C-) 1-0326-	(J3WE) 1-0378-W	-327	-55	-328	-329	-330	-340	-350	—	K1	
(UPL20-) 1-0369-U	(UPL20-) 1-0369-U	-351	-66	-56	-352	-353	-354	-355	-356	K1	
(PL94-) 1-0029-	(PL1C-) 1-0326-	-357	-358	-359	-57	-360	-361	-362	-363	K1	
(PL11C-) 1-0326-	(UPL20-) 1-0369-U	-364	-58	-365	-366	-367	-368	-369	-370	K1	
(PL40-) 1-0014-	(PL40-) 1-0014-	-84	-371	-372	-59	-112	-373	-192	-374	K1	
(PL20-) 1-0369-	(RT ANG SMA) DSM531-2	-60	—	—	—	-105	—	-382	—	K1	
(PL1WC-) 1-0453-W	(PL11C-) 1-0326-	-375	-61	-376	-377	-378	-379	-380	-381	K1	
(PL20-) 1-0369-	(RT ANG BNC(M)) 31-335	-65	—	—	—	-107	—	-383	—	K1	
(MP3W-) 1-0410-W	(MP3W-) 1-0410-W	-67	-68	-384	—	-108	-385	-386	—	K1	
(J3WE-) 1-0378-W	—	-387	-69	-388	-389	-390	-391	-392	—	K2	
(PL20-) 1-0369-	(F59A)	—	-70	-393	—	—	—	—	—	K1	
(PL40-) 1-0014-	(PL60-) 1-0353-	-71	—	—	-394	-109	—	-396	-397	K1	
(PL123-) 1-0390-	(PL123-) 1-0390-	-72	-73	-75	-212	-110	-398	-399	-400	K1	
(UPL123-) 1-0390-U	(UPL123-) 1-0390-U	-401	-74	-76	-402	-403	-404	-405	-406	K1	
(PL95-) 1-0370-	(PL20-) 1-0369-	-120	-78	-407	-201	-408	-409	-410	-411	K1	
(PL95-) 1-0370-	(PL1WC-) 1-0453-W	-412	-79	-413	-414	-415	-416	-417	-418	K1	
(PL60-) 1-0353-	(BJ69-) 1-0355-	-80	—	—	-395	-111	—	-419	-420	K1	
(PL11C-) 1-0370-	(PL50-) 1-0016-	-421	-81	-422	-423	-424	-425	-426	—	K1	
(PL20-) 1-0369-	—	-214	-427	-83	-233	-428	-429	-430	-431	K2	
(PL95-) 1-0370-	(PL130-) 105-0181-	-432	-85	-433	-434	-435	-436	-437	—	K1	

CONNECTOR P1 DESCRIPTION/ PART NO	CONNECTOR P2 DESCRIPTION/ PART NO	CABLE GROUPS; WRENCH CRIMP, (TODL CRIMP)								CKT CODE
		1(011)	2(013A)	2(013/013B)	3(012)	1(011)	2(013)	1(012)	2(011)	
		TCC-50-2	TCC-75-2	RG62	M17/167-00001 (RG623)	RG58 BLACK	RG59 BLACK	RG142	RG303	
11-01 DASH NUMBERS										
(PL1C-) 1-0453- (BJ29-) 1-0126- (UPL20-) 1-0369-U (UPL20-) 1-0369-U (UPL123-) 1-0390-U (PL20-) 1-0369- (PL20-) 1-0369- (UPL40-) 1-0014-U (UPL40-) 1-0014-U (J12NMF-) 105-0910- (J3E-) 1-0378- (PL20-) 1-0369- (UPL95-) 1-0370-U (UPL95-) 1-0370-U (PL220-) 1-0442- (PL220-) 1-0442- (PL220-) 1-0442- (PL223-) 1-0009- (UPL223-) 1-0050- (UPL220-) 1-0468- (PL223-) 1-0009- (UPL223-) 1-0050- (UPL220-) 1-0468- (UPL220-) 1-0468-	(UG536 B/U) A (PL20-) 1-0369- A (PL1C-) 1-0453- A (PL1WC-) 1-0453-W A (PL1C-) 1-0453- A (BJ95-) 1-0175- A (PL11C-) 1-0326- A (PL11C-) 1-0326- A (PL1WC-) 1-0453-W A (PL1WC-) 1-0453-W A (PL20-) 1-0369- A (PL75-1 FDS) 305-0111-1 A (PL11C-) 1-0326- A (PL1WC-) 1-0453-W A (PL1WC-) 1-0453-W A (PL220-) 1-0442- A (PL220-) 1-0442- A (PL220-) 1-0442- A (PL1C-) 1-0453- A (PL1WC-) 1-0453-W A (UPL220-) 1-0468- A (PL223-) 1-0009- A (UPL223-) 1-0050- A (PL1C-) 1-0453- A (PL1WC-) 1-0453-W A	-86 -128 A -444 A -450 A -456 A -121 A -469 A -476 A -483 A -490 A -496 A -127 A -504 A -511 A -131 A -134 A -137 A -140 A -143 A -537 A -148 A -547 A -553 A -559 A	— -438 B -114 C -116 C -118 A -462 B -122 B -123 B -124 C -125 A -497 B — -129 A -130 A -132 A -135 A -138 E -141 A -144 A -147 A -150 A -153 E -155 A	— -439 B -115 C -117 C -119 A -463 B -470 B -477 B -484 C -491 A -126 B — -505 A -512 A -133 A -136 A -139 E -142 A -145 A -146 A -151 A -152 A -154 C	— -440 A -445 A -451 A -457 A -464 A -471 A -478 A -485 A -492 A -498 A — -506 A -513 A -518 A -522 A -197 A -529 A -533 A -538 A -543 A -548 A -554 A -560 A	— -87 A -446 A -452 A -458 A -465 A -472 A -479 A -486 A -493 A -499 A -500 A -502 A -507 A -514 A -159 A -160 A -161 A -162 A -163 A -539 A -164 A -549 A -555 A -561 A	— -441 B -447 C -453 A -459 A -466 B -473 B -480 B -487 C -494 A -509 B — -509 A -515 A -519 A -523 A -526 E -530 A -534 A -540 A -544 A -550 A -556 E -562 A	— -442 A -448 A -454 A -460 A -467 A -474 A -481 A -488 A -495 A -501 A — -503 A -508 A -516 A -520 A -524 A -527 A -531 A -535 A -541 A -545 A -551 A -557 A -563 A	— -443 A -449 A -455 A -461 A -468 A -475 A -482 A -489 A — 	

IF PLASTIC STRAIN RELIEF IS REQUIRED, SUFFIX PART NO WITH BT, ADD 1 STRAIN RELIEF EACH CONNECTOR AS FOLLOWS:

- ACA1
- ACA2
- ACB013-7 FOR VIOLET CABLE ALL OTHERS USE -0 BLACK
- ACC011
- ACC013

WHEN ASSEMBLY IS ORDERED BY MODEL NO ADD ACB013-7 PLASTIC STRAIN RELIEF 2 PER EACH CABLE ASSY

9. EXAMPLE OF COMPLETE PART NO:

11-01- X - YEL
DASH NO

8. SEE 11-08 FOR CABLE ASSEMBLIES WITH BEND RELIEF SPRING(S)

- JERROLD
- BELL IND
- H.H SMITH
- AMPHENOL

IDENTIFY PER MARKING TABLE CENTER ONLY ON CABLES 60 INCHES OR LESS; AT BOTH ENDS ON CABLES OVER 60 INCHES LONG

2. SEE CONN DWG FOR CABLE STRIPPING & ASSY INSTRUCTIONS

LENGTH IN INCHES
TOL PER TT-03

INSTALL ACA1 -0 BOOT OVER CONNECTOR CRIMP.

PIGTAIL UN-TERMINATED END USING 3' EACH 700-0094 + 700-0095 HOOK-UP WIRE.

SWITCHCRAFT

MALE 'F' CONN (PL210HB-AUGAT LRC)

CUSTOMER FURNISHED CONNECTORS (ALLIED SIGNAL)

SMB CONNECTOR, ITT CANNON RF PRODUCTS OR EQUIV

EF JOHNSON

IF ALTERNATIVE COLOR IS REQUIRED, SUFFIX P/N WITH COLOR DESIGNATION AND REPLACE TCC-75-2 WITH APPROPRIATE CABLE AS FOLLOWS:

BLK FOR TCC-75-2 BLACK
BLU FOR TCC-75-2 BLUE
GRN FOR TCC-75-2 GREEN
RED FOR TCC-75-2 RED
YEL FOR TCC-75-2 YELLOW

IF COLORED 50 OHM CABLE IS REQUIRED, REPLACE TCC-50-2 WITH THE FOLLOWING:
RED: RG58/RED
BLUE:

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[PC-12-75](#) [PC-24-75](#) [PC-18-75](#) [PCX-24-50](#) [PC-6-50](#)