

- Compact encapsulated 65 Watt PCB module (3.2"x2.2")
- I/O isolation 4000 VAC rated for 250 VAC working voltage
- Certification according to IEC/EN/ES 60601-1 edition 3.2 for 2 x MOPP
- Risk management process according to ISO 14971 incl. risk management file
- Acceptance criteria for electronic assemblies acc. to IPC-A-610 Level 3
- Low leakage current <100 µA rated for BF applications
- Operating temperature -40°C to 80°C
- EMC compliance according to IEC 60601-1-2 4th edition and EN 55032 class B
- Operating up to 5000 m altitude
- 5-year product warranty



ES 60601-1 IEC 60601-1
UL 62368-1 IEC 62368-1

The TPP 65E-D is a 65 Watt encapsulated AC/DC modules in a PCB package. It features a reinforced double I/O isolation system according to latest medical safety standards (60601-1 edition 3.2, 2 x MOPP). The leakage current is below 100 µA and makes the module suitable for BF (body floating) applications. The excellent efficiency of up to 94% allows a high power density and compact design (3.2" x 2.2"). The operating temperature range is -40°C to +80°C with derating above 60°C. The EMC characteristic is dedicated for applications in industrial and medical fields. High reliability is provided by use of high quality components and an excellent thermal management making the TPP 65E-D an ideal solution for medical devices and for demanding safety and space critical applications.

Models				
Order Code	Output Power max.	Output Voltage nom. (adjustable)	Output Current max.	Efficiency typ.
TPP 65-105E-D	50 W	5 VDC (4.5 - 5.5 VDC)	10'000 mA	90 %
TPP 65-112E-D	65 W	12 VDC (10.8 - 13.2 VDC)	5'420 mA	93 %
TPP 65-115E-D		15 VDC (13.5 - 16.5 VDC)	4'340 mA	94 %
TPP 65-124E-D		24 VDC (21.6 - 26.4 VDC)	2'710 mA	94 %
TPP 65-136E-D		36 VDC (32.4 - 39.6 VDC)	1'810 mA	93 %
TPP 65-148E-D		48 VDC (43.2 - 52.8 VDC)	1'360 mA	93 %

Input Specifications

Input Voltage	- AC Range	Operational Range: 85 - 264 VAC (Full Range) Rated Range: 100 - 240 VAC (Full Range)
	- DC Range	Operational Range: 120 - 370 VDC (Designed for, no certification) Polarity: +DC: L / -DC: N
Input Frequency		Operational Range: 47 - 440 Hz Certified: 50/60 Hz
Power Consumption	- No load & Vin = 230 VAC	210 mW max. (Ready to meet ErP directive)
	- No load & Vin = 115 VAC	210 mW max.
Input Current	- Full load & Vin = 230 VAC	900 mA max.
	- Full load & Vin = 115 VAC	1'500 mA max.
Input Inrush Current	- At 230 VAC	80 A max.
	- At 115 VAC	30 A max.
Input Protection		T 3.15 A / 250 VAC (Internal Fuse L & N)
Recommended Input Fuse		3'150 mA (slow blow) (The need of an external fuse has to be assessed in the final application.)

Output Specifications

Output Voltage Adjustment		±10% (By external trim resistor) See application note: www.tracopower.com/overview/tpp65e-d Output power must not exceed rated power!
Voltage Set Accuracy		±1% max.
Regulation	- Input Variation (Vmin - Vmax)	0.2% max.
	- Load Variation (0 - 100%)	0.5% max.
Ripple and Noise (20 MHz Bandwidth)	5 VDC model:	100 mVp-p max. (w/ 10 µF)
	12 VDC model:	100 mVp-p max. (w/ 10 µF)
	15 VDC model:	100 mVp-p max. (w/ 10 µF)
	24 VDC model:	120 mVp-p max. (w/ 1 µF)
	36 VDC model:	120 mVp-p max. (w/ 1 µF)
	48 VDC model:	200 mVp-p max. (w/ 0.1 µF)
	5 VDC model:	75 mVp-p typ. (w/ 10 µF)
	12 VDC model:	75 mVp-p typ. (w/ 10 µF)
	15 VDC model:	75 mVp-p typ. (w/ 10 µF)
	24 VDC model:	75 mVp-p typ. (w/ 1 µF)
	36 VDC model:	75 mVp-p typ. (w/ 1 µF)
	48 VDC model:	150 mVp-p typ. (w/ 0.1 µF)
	5 VDC model:	20'000 µF max.
	12 VDC model:	4'520 µF max.
	15 VDC model:	2'900 µF max.
	24 VDC model:	1'130 µF max.
Capacitive Load	36 VDC model:	520 µF max.
	48 VDC model:	285 µF max.
Minimum Load		Not required
Temperature Coefficient		±0.02 %/K max.
Hold-up Time	- At 230 VAC	75 ms min.
	- At 115 VAC	16 ms min.
Start-up Time	- At 230 VAC	1'000 ms max.
	- At 115 VAC	1'000 ms max.
Short Circuit Protection		Continuous, Automatic recovery
Output Current Limitation		120 - 180% of Iout max.
		145% typ. of Iout max.
Overvoltage Protection		125 - 140% of Vout nom.
		130% typ. of Vout nom.

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Transient Response	- Response Deviation	3% max. (50% to 75% Load Step at 2.5 A/μs)
	- Response Time	600 μs typ. (50% to 75% Load Step at 2.5 A/μs)

Safety Specifications

Standards	- IT / Multimedia Equipment	EN 62368-1 IEC 62368-1 UL 62368-1
	- Medical Equipment	EN 60601-1 IEC 60601-1 ANSI/AAMI ES 60601-1 2 x MOPP (Means Of Patient Protection) www.tracopower.com/overview/tpp65e-d
	- Certification Documents	
Protection Class		Class I & II (Prepared): Reinforced Insulation
Pollution Degree		PD 2
Over Voltage Category		OVC II

EMC Specifications

EMI (Emissions)	- Conducted Emissions	EN 60601-1-2 edition 4 (Medical Devices) EN 55011 class B (internal filter) EN 55032 class B (internal filter) FCC 47 Part 15 class B (internal filter) FCC 47 Part 18 class B (internal filter)
	- Radiated Emissions	EN 55011 class B (internal filter) EN 55032 class B (internal filter) FCC 47 Part 15 class B (internal filter) FCC 47 Part 18 class B (internal filter)
	- Harmonic Current Emissions	EN 61000-3-2, class A
	- Voltage Fluctuations & Flicker	EN 61000-3-3
EMS (Immunity)	- Electrostatic Discharge	EN 60601-1-2 edition 4 (Medical Devices) Air: EN 61000-4-2, ±15 kV, perf. criteria A Contact: EN 61000-4-2, ±8 kV, perf. criteria A EN 61000-4-3, 20 V/m, perf. criteria A EN 61000-4-4, ±2 kV, perf. criteria A
	- RF Electromagnetic Field	L to L: EN 61000-4-5, ±1 kV, perf. criteria A EN 61000-4-6, 20 Vrms, perf. criteria A
	- EFT (Burst) / Surge	Continuous: EN 61000-4-8, 30 A/m, perf. criteria A 230 VAC / 50 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 1 period, perf. criteria A >95%, 250 periods, perf. criteria B
	- Conducted RF Disturbances	115 VAC / 60 Hz: EN 61000-4-11 30%, 25 periods, perf. criteria A >95%, 0.5 periods, perf. criteria A >95%, 1 period, perf. criteria A >95%, 250 periods, perf. criteria B
	- PF Magnetic Field	
	- Voltage Dips & Interruptions	
EMC / Environmental	- Certification Documents	www.tracopower.com/overview/tpp65e-d

General Specifications

Relative Humidity		95% max. (non condensing)
Temperature Ranges	- Operating Temperature	-40°C to +85°C
	- Storage Temperature	-40°C to +85°C
Power Derating	- High Temperature	Depending on model
	- Low Input Voltage	Depending on model
	See application note:	www.tracopower.com/overview/tpp65e-d
Cooling System		Natural convection (20 LFM)

All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Altitude During Operation	5'000 m max.
Regulator Topology	Flyback Converter
Switching Frequency	50 - 130 kHz (PWM QR)
Insulation System	Reinforced Insulation
Working Voltage (rated)	250 VAC
Isolation Test Voltage	- Input to Output, 60 s - Input to Case or PE, 60 s - Output to Case or PE, 60 s
Creepage	- Input to Output - Input to Case or PE - Output to Case or PE
Clearance	- Input to Output - Input to Case or PE - Output to Case or PE
Isolation Resistance	- Input to Output, 500 VDC
Isolation Capacitance	- Input to Output, 100 kHz, 1 V
Leakage Current	- Touch Current
Reliability	- Calculated MTBF
Washing Process	According to Cleaning Guideline www.tracopower.com/info/cleaning.pdf
Environment	- Vibration - Mechanical Shock - Thermal Shock
Housing Material	Plastic (UL 94 V-0 rated)
Potting Material	Silicone (UL 94 V-0 rated)
Pin Material	Tinned Copper
Pin Foundation Plating	Nickel (2 - 3 µm)
Pin Surface Plating	Tin (3 - 5 µm), matte
Housing Type	Plastic Case
Mounting Type	PCB Mount
Connection Type	THD (Through-Hole Device)
Soldering Profile	Lead-Free Wave Soldering 260°C / 6 s max.
Weight	265 g
Environmental Compliance	- REACH Declaration - RoHS Declaration - SCIP Reference Number


Supporting Documents

Overview Link (for additional Documents)

www.tracopower.com/overview/tpp65e-d


All specifications valid at 230 VAC, resistive full load and +25°C after warm-up time, unless otherwise stated.

Outline Dimensions



Pinout	
Pin	Function
1	AC (N)
2	AC (L)
4	Trim
5	-Vout
6	+Vout

All dimensions in mm (inch)
 Tolerance: x.x ±0.5 (x.xx ±0.02)
 x.xx ±0.25 (x.xxx ±0.010)



Suggested screw: ST2.9 X 6.5
 Mounting screw locked torque: Max. 0.33 Nm (3.4 kgfcm)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TRACO Power:](#)

[TPP 65-105E-D](#) [TPP 65-112E-D](#) [TPP 65-115E-D](#) [TPP 65-124E-D](#) [TPP 65-136E-D](#) [TPP 65-148E-D](#)