


- Very compact metal cased power supplies
- High operating temperature up to 70°C
- Low no load power consumption <0.5W
- Screw terminal block
- No internal fan
- Universal AC input
- Withstand 300 VAC surge input for 5 sec.
- Adjustable output voltage
- 3-year product warranty



The TXM 015 series of 15 Watt is a family of enclosed AC/DC power supplies designed for cost critical applications. With a low profile metal case and screw terminal block connections, they are easy to install in any equipment. There are five models of single output voltages from 3.3 VDC to 24 VDC. These power supplies have universal input and comply with European EMC standards and the Low Voltage Directive (LVD).

Models				
Order Code	Output Power (max.)	Output Voltage (adjustable)	Output Current (max.)	Efficiency (typ.)
TXM 015-103	15 Watt	3.3 VDC	4.0 A	71 %
TXM 015-105		5 VDC	3.0 A	78 %
TXM 015-112		12 VDC	1.3 A	82 %
TXM 015-115		15 VDC	1.0 A	83 %
TXM 015-124		24 VDC	0.7 A	85 %

Input Specifications

Input voltage range	– AC range (universal input) – DC range	88 – 264 VAC (47 – 63 Hz) 124 – 370 VDC
Input current at full load		0.7 A max.
Surge voltage (5 s max.)		300 VAC
Inrush current	– at 115 VAC – at 230 VAC	20 A max. 40 A max.
Zero load power consumption		0.5 W max.
Leakage current	– Input to Output – Input to PE	0.25 mA max. 3.50 mA max.

Output Specifications

Voltage set accuracy	3.3 & 5 Vout models: other output models:	±2 % max. ±1 % max.
Voltage adjustment range		–5 % to +10 %
Regulation	– Input variation (Vin min. to Vin max.) – Load variation (0 to 100%)	0.5 % max. 3.3 & 5 Vout models: other output models:
Minimum load		not required
Temperature coefficient		±0.03 %/K max.
Hold-up time	– at 115 VAC – at 230 VAC	10 ms min. 20 ms min.
Start-up time	– at 115 VAC – at 230 VAC	2 s max. 1 s max.
Startup overshoot voltage		5 % max.
Ripple and noise (20 MHz Bandwidth)	3.3 & 5 Vout models: other output models:	50 mVp-p max. 120 mVp-p max.
Output current limitation		105 – 150 % of Iout
Short circuit protection		continuous, automatic recovery (hiccup mode)
Over voltage protection		105 – 150 % of Vout (constant voltage)


All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

General Specifications

Temperature ranges	– Operating	–25°C to +70°C
	– Storage	–40°C to +85°C
Humidity (non condensing)	– Operating	20 – 90 % rel. H
	– Storage	10 – 95 % rel. H
Altitude during operation		2000 m max.
Isolation voltage	– Input to output (60 s)	3000 VAC
	– Input to case (60 s)	1500 VAC
	– Output to case (60 s)	500 VAC
Isolation resistance		100 MOhm min.
Reliability	– Calculated MTBF at +25°C acc. to MIL-HDBK-217F	200'000 h
Protection class		class I
EMC emissions	– Conducted and radiated input emission	EN 55032, class B
	– Flicker	EN 61000-3-3
EMC immunity		EN 55024
	– Electrostatic discharge (ESD)	EN 61000-4-2, ±4 kV air, ±8 kV contact perf. criteria A
	– Radiated immunity	EN 61000-4-3, 3 V/m perf. criteria A
	– Fast transiente	EN 61000-4-4, ±1 kV perf. criteria A
	– Surge	EN 61000-4-5, ±1 kV line to line, ±2kV line to ground, perf. criteria A
	– Conducted immunity	EN 61000-4-6, 3 Vrms perf. criteria A
	– Magnetic field immunity	EN 61000-4-8, 3 A/m perf. criteria A
Safety standards and certification		EN 61000-4-11
	– Certification documents	IEC/EN/UL 60950-1 www.tracopower.com/overview/txm015
Environmental compliance	– Reach	www.tracopower.com/info/reach-declaration.pdf
	– RoHS	RoHS directive 2011/65/EU
Connection		Screw terminal

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Dimension



Pin-Out	
Pin	Function
1	AC (L)
2	AC (N)
3	PE
4	- Vout
5	+ Vout

Weight: 165 g (5.82 oz)

Dimensions in mm (inch)
Outside dimension tolerance: ± 1.0 mm (± 0.04)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TRACO Power:

[TXM 015-103](#) [TXM 015-105](#) [TXM 015-112](#) [TXM 015-115](#) [TXM 015-124](#)