

DMC7 (M83507/11-01) ELECTRICAL CONTACT TOOL KIT



**DMC7
(M83507/11-01)
NSN: 5180-00-921-5771**

The DMC7 kit supplies your staff with the tools and accessories necessary for the Mil Spec M83507/11-01.

The DMC AF8, qualified to MIL-DTL-22520/1, has virtually limitless application within the specified wire range of 12 through 26 AWG. The 8 impression crimp, which is standard in the AF8, assures absolute maximum tensile strength with almost every closed barrel contact. Over a thousand turret heads are available to adapt the tool frame to your specific military or proprietary contact/wire combination.





The precision ratchet controls cycling of the tool in both directions of handle movement. This assures the same accurate crimp every time.

Positive crimp depth is controlled by an 8 position selector knob conveniently located on the tool frame. The operator simply dials the desired step for the wire being used. This setting can be secured by use of a locking pin or safety wire.

TOOL KIT CONFIGURATION

Type of Case	Portable
Number of Cases	1
Color	Grey
Type of Construction	Steel/Aluminum
Application	M83507/11-01
Type of Inserts	4101 Fire Retardant Etha Foam with Die Cut Tool Cavities

DMC7 TOOL AND ACCESSORY LIST

	1	Crimp Tool
	2	Turret heads
	1	9/64" Hex Wrench
	1	In-Service Inspection Gage

5180-00-921-5771

DMC7



DMC **DANIELS
MANUFACTURING
CORPORATION** ®

DANIELS MANUFACTURING CORP., 526 THORPE ROAD, ORLANDO, FL 32824, USA
PHONE (407) 855-6161 • FAX (407) 855-6884 • www.DMCTools.com • E-MAIL: DMC@DMCTools.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Daniels Manufacturing:](#)

[DMC7](#)