






UNCONTROLLED DOCUMENT
WILL NOT BE UPDATED



INSERT COLOR	HOLE DIMENSIONS	ADDITIONAL FEATURES
RED	Ø.080 ▽THRU	└┐Ø.100 ▽.068
BLACK	Ø.125 ▽THRU	└┐Ø.141 ▽.105
SILVER	BLANK	

GLENAIR CONTACT	COLOR CODE	20	16	WIRE SIZE
10-374-20; 10-375-20 10-571-20; 10-573-20	RED	5		SELECTOR No.
10-374-16; 10-375-16 10-571-16; 10-573-16	BLUE		6	

DATAPLATE

NOTE: FOR USE WITH DANIELS CRIMP TOOLS
ACCOMMODATING "TH" SERIES POSITIONERS

RESTRICTED & CONFIDENTIAL CONFIDENTIAL PROPERTY OF DANIELS MANUFACTURING CORP. NOT TO BE DISCLOSED TO OTHERS, REPRODUCED OR USED FOR ANY OTHER PURPOSE EXCEPT AS AUTHORIZED IN WRITING BY DANIELS MANUFACTURING. MUST BE RETURNED TO DANIELS MANUFACTURING CORP. ON COMPLETION OF ORDER OR OTHER PURPOSE FOR WHICH LENT.		MATERIAL		ITEM		PART NO.		QTY.		DESCRIPTION/REMARKS	
HEAT TREAT		DRN.		DATE		05-04-10		DATE		DANIELS MANUFACTURING CORP. ORLANDO, FLORIDA CAGE 11851	
		CHK'D.		DATE							
		APP'D.		DATE							
		APP'D.		DATE							
FINISH		NOTE:		THIS DRAWING IS AN OUTLINE DRAWING OF THE RESPECTIVE DMC PART NUMBER INDICATED. ACTUAL DMC PART NUMBER IS DRAWING NUMBER WITHOUT THE "-ENV" SUFFIX		WHERE USED: AF8		SIZE		SCALE	
								B		1.5X	
										CAD P/N	
										TH721-ENV	
										SHEET OF	
										1 1	
										REV.	
										1	

DO NOT SCALE DRAWING

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Daniels Manufacturing:](#)

[TH721](#)