






RED INDICATES ORIGINAL

DATA CONTAINED IN THIS DOCUMENT IS UNCLASSIFIED EXCEPT WHERE SHOWN OTHERWISE AND SHALL NOT BE DISTRIBUTED OUTSIDE OF THE U.S. GOVERNMENT WITHOUT EXPRESS WRITTEN PERMISSION.		REV E0		REVISIONS		1-0505		SH 1	
C		0		ITEM 3 WAS 8-2021;		OWN APPROVED		DATE	
				SEE ECO		DKC		4/11/97	

MODEL NO	ACCEPTS PIN DIA	RECEPTACLE TYPE
J24	.070 RCA	BNC
J24W	.090 AT&T	
J24H	.070 RCA	TNC
J24WH	.090 AT&T	



J24W SHOWN



4. EXAMPLE OF COMPLETE MODEL NO:
J24W
- BASIC MODEL NO
(SEE TABLE)
3. DUAL COAXIAL NORMAL THRU PATCH JACK WITH BNC/TNC RECEPTACLES
2. FINISH: TFS-1A (NICKEL)
1. ALL DIM ARE IN INCHES

INCH	MM
.005	0.13
.010	0.25
.030	0.76
.070	1.78
.090	2.20
.156	3.96
.445	11.30
.487	12.37
.562	14.27
.570	14.48
.625	15.88
1.148	29.16
1.375	34.92
1.659	42.14
2.880	67.56

QTY	DESCRIPTION	PART NUMBER	ITEM
TOL UNLESS SPECIFIED	TROMPETER		
.XXX ± .005	ELECTRONICS, INC.	J24/J24W/J24H/J24WH	
ANALOG			
OWN DKC 3-21-87	MATERIAL	CODE IDENT	REV
CHK DKC 10/1/97	14949	14949	1-0505
ENGR			D
APPR			
NEXT ASSY		DATE 9-17-92	SHEET 1 OF 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cinch Connectivity Solutions:](#)

[J24](#)