


Specification Sheet

Part Number: 111-01167



- Total metal dispersion throughout the tie available in a wide range of sizes
- Usable as part of HACCP process
- Greatly reduces risk of contamination
- Magnetic and X-Ray detectable versions available

Metal Content Tie, 15" Long, 50lb Tensile Strength, PA66MP, Red, 100/pkg

Article Number	111-01167
Type	MCT50L
Color	Red (RD)
Quantity Per	bag
Product Description	HellermannTyton's Metal Content Tie is specifically designed for the food, beverage and pharmaceutical processing industries to meet the safety standards set by the Hazardous Analysis of Critical Control Point (HACCP). The tie is nylon-based with metal content dispersed throughout the head and strap allowing any part of the tie to be identified by metal detectors or X-ray inspections, reducing the risk of contamination.
Short Description	Metal Content Tie, 15" Long, 50lb Tensile Strength, PA66MP, Red, 100/pkg

Global Part Name	MCT50L-PA66MP-RD
-------------------------	------------------

Minimum Tensile Strength (Imperial)	50.0
--	------

Minimum Tensile Strength (Metric)	225
--	-----

Length L (Imperial)	15.0
----------------------------	------

Length L (Metric)	380.0
--------------------------	-------

Fixation Method	Cable Tie
------------------------	-----------

Identification Plate Position	none
--------------------------------------	------

Releasable Closure	No
---------------------------	----

Tie Closure	plastic pawl
--------------------	--------------

Variant	Inside Serrated
----------------	-----------------

Width W (Imperial)	0.19
---------------------------	------

Width W (Metric)	4.7
-------------------------	-----

Bundle Diameter Min (Imperial)	0.06
---------------------------------------	------

Bundle Diameter Min (Metric)	1.5
-------------------------------------	-----

Bundle Diameter Max (Imperial)	4.3
---------------------------------------	-----

Bundle Diameter Max (Metric)	110.0
-------------------------------------	-------

Thickness T (Metric)	1.4
Material	Polyamide 6.6, with metal particles (PA66MP)
Material Shortcut	PA66MP
Flammability	UL 94 HB
Halogen Free	Yes
Operating Temperature	-40°F to +185°F (-40°C to +85°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	100
Package Quantity (Metric)	100

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[111-01167](#)