

## Specification Sheet

Part Number: T150LL0UVX2



UV stabilized heavy duty cable ties contain an inhibitor which prolongs the life of the tie in UV exposures.

Head design provides high tensile strength with very low insertion force.

Heavy Duty Cable Tie, 36" Long, UL Rated, 175lb Tensile Strength, PA66UV, Black, 25/pkg

|                |           |
|----------------|-----------|
| Article Number | 111-15704 |
|----------------|-----------|

|      |        |
|------|--------|
| Type | T150LL |
|------|--------|

|       |            |
|-------|------------|
| Color | Black (BK) |
|-------|------------|

|              |      |
|--------------|------|
| Quantity Per | pack |
|--------------|------|

|                     |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                               |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Product Description | Used in the solar industry and other applications, HellermannTyton offers cable ties made of UV stabilized PA66UV material. This material provides additional protection against UV radiation for long-term outdoor use and is available in various styles, tensile strengths, and bundle diameters. T-Series cable ties feature inside serrations to provide a positive hold on wire and cable bundles. The head design guarantees high tensile strength and a low insertion force. For high-volume applications, tensioning tools are available to ensure consistent and safe installation. |
|---------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                                     |                                                                                         |
|-------------------------------------|-----------------------------------------------------------------------------------------|
| Short Description                   | Heavy Duty Cable Tie, 36" Long, UL Rated, 175lb Tensile Strength, PA66UV, Black, 25/pkg |
| Global Part Name                    | T150LL-PA66UV-BK                                                                        |
| Minimum Tensile Strength (Imperial) | 175                                                                                     |
| Minimum Tensile Strength (Metric)   | 780                                                                                     |
| Length L (Imperial)                 | 36.4                                                                                    |
| Length L (Metric)                   | 925.0                                                                                   |
| Identification Plate Position       | none                                                                                    |
| Releasable Closure                  | No                                                                                      |
| Tie Closure                         | plastic pawl                                                                            |
| Variant                             | Inside Serrated                                                                         |
| Width W (Imperial)                  | 0.35                                                                                    |
| Width W (Metric)                    | 8.9                                                                                     |
| Bundle Diameter Min (Imperial)      | 0.31                                                                                    |
| Bundle Diameter Min (Metric)        | 8.0                                                                                     |
| Bundle Diameter Max (Imperial)      | 10.8                                                                                    |
| Bundle Diameter Max (Metric)        | 274.3                                                                                   |

|                               |                                     |
|-------------------------------|-------------------------------------|
| Material                      | Polyamide 6.6 UV-resistant (PA66UV) |
| Material Shortcut             | PA66UV                              |
| Flammability                  | UL 94 HB                            |
| Halogen Free                  | Yes                                 |
| UV Resistant (Yes/No)         | Yes                                 |
| Use Conditions                | For Indoor and Outdoor Use          |
| Plenum Rating                 | AH-2                                |
| Operating Temperature         | -40°F to +185°F (-40°C to +85°C)    |
| Reach Compliant (Article 33)  | Yes                                 |
| ROHS Compliant                | Yes                                 |
| Certification/Specification   | UL 62275                            |
| UL Recognized (US)            | Yes                                 |
| UL Recognized (US and Canada) | Yes                                 |
| Package Quantity (Imperial)   | 25                                  |
| Package Quantity (Metric)     | 25                                  |

Customs Number

3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: [corp@htamericas.com](mailto:corp@htamericas.com)

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#)   [RoHS/WEEE Compliance](#)   [Disclaimer](#)   [Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[T150LL0UVX2](#)