






SW2011



Revision level		Revision Record	Changed	Date	Approved	Date
Drawing	Part					
02	K	SEE ECN# 012243	CJR	01/03/2013	CJR	01/03/2013

2


 12.8 ± 0.3
 $[\.504 \pm .012]$

 28.1 ± 0.7
 $[1.11 \pm .03]$
 1.4 ± 0.1
 $[\.06 \pm .004]$

 19.1 ± 0.3
 $[\.75 \pm .01]$
 19.7 ± 0.3
 $[\.78 \pm .01]$

 FLAT LENGTH
 SEE TABLE

PART NUMBER	FLAT LENGTH mm [in]	MIN LOOP TENSILE STRENGTH - N [lbs]
DCT9	331.0 $\pm$ 5.0 [13.03 $\pm$ 0.2]	667 N [150 lbs]
DCT11	489.0 $\pm$ 5.0 [19.25 $\pm$ 0.2]	667 N [150 lbs]

 Material
 PA66HIRHSUV

Units: millimeters

Tolerance defined on
each dimension

The copyright of this
drawing is reserved by
HellermannTyton. It is
issued on condition that it is
not reproduced, copied, or
disclosed to a third party,
either wholly or in part,
without the consent of
HellermannTyton.

Drawn	WPT	02/20/2012
Approved	WPT	04/04/2012

HellermannTyton

 North America
 Email: corp@htamericas.com
 Web: www.hellermann.tyton.com

2

Article/Type-No	SEE TABLE	Scale	1:1
Title	DUAL CLAMP TIE WITH 1/4" MOUNTING HOLE	Project Number	PRP 12-0008
Drawing-No	12-0008-001-CSU	Format	AH
Production : Phase		Sheet	1/1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[DCT90HIRC2](#)