

Specification Sheet

Part Number: 157-00366



Off-Set design allows bundles to sit off of mounting points to avoid friction against surrounding areas.

Fir tree gives 3 to 1 extraction versus insertion force making them strong and easy to install.

Friction tab inside of fir tree allows tie to sit in mount without falling out prior to installation.

1-Pc Cable Tie/Fir Tree Mount w/Disc, 12.5mm Offset, 8.5"L, 6.1-7mm Hole, PA66HIRHS, Gray, 3000/ctn

Article Number	157-00366
----------------	-----------

Type	T50ROSFT6SO12.5A
------	------------------

Color	Gray (GY)
-------	-----------

Quantity Per	bag
--------------	-----

Product Description	HellermannTyton's Off-Set Fir Tree Cable Tie and fixing offers a simple and easy to use method of bundling and fixing cables, the design of the fir tree ensures a positive and secure fixing into panels with thicknesses from .2" - .26" or threaded blind holes. The 'disc' on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.
---------------------	--

Short Description	1-Pc Cable Tie/Fir Tree Mount w/Disc, 12.5mm Offset, 8.5"L, 6.1-7mm Hole, PA66HIRHS, Gray, 3000/ctn
-------------------	---

Global Part Name	T50ROSFT6SO12.5A-PA66HIRHS-GY
------------------	-------------------------------

Minimum Tensile Strength (Imperial)	50.0
-------------------------------------	------

Minimum Tensile Strength (Metric)	225.0
-----------------------------------	-------

Length L (Imperial)	8.5
---------------------	-----

Length L (Metric)	215.9
-------------------	-------

Offset Length (Imperial)	0.49
--------------------------	------

Offset Length (Metric)	12.5
------------------------	------

Fixation Method	Fir Tree
-----------------	----------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Width W (Imperial)	0.19
--------------------	------

Width W (Metric)	5.1
------------------	-----

Bundle Diameter Min (Imperial)	0.08
--------------------------------	------

Bundle Diameter Min (Metric)	2.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.97
--------------------------------	------

Bundle Diameter Max (Metric)	50.0
------------------------------	------

Height H (Imperial)	0.87
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.26
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.65
Mounting Hole Diameter D (Imperial)	0.24 - 0.28 ";0.24 - 0.26
Mounting Hole Diameter D (Metric)	6.35 mm (hexagonal) 6.1 - 7.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.28 ";0.26
Mounting Hole Diameter D Max (Metric)	7.0
Disc Diameter (Metric)	15.0
Disc Diameter (Imperial)	0.59
Material	Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS)
Material Shortcut	PA66HIRHS
Operating Temperature	-40°F to +230°F (-40°C to +110°C)

ROHS Compliant	Yes
Package Quantity (Imperial)	3000
Package Quantity (Metric)	3000
Customs Number	3926909988

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00366](#)