

Specification Sheet

Part Number: 157-00370

All-in-one bundling and fastening solution reduces costs and assembly time.

Anti-rotational oval fastener forces bundle to travel in intended direction.

High-spec materials and superior design deliver excellent performance and value.

The disc on the top of the fir tree covers the hole and minimizes the ingress of water and dirt.

The oval hole fir tree fits four common automotive oval hole sizes.

The specific connector slot on this part reduces rattle and movement of clip to the wire harness connector.



1-Pc Cable Tie/Fir Tree Mount with Disc, 6.6"L, 6.2 - 13.0 mm, PA66HS, Black, 1000/bag

Article Number	157-00370
Type	T50SOSFTOVALU
Color	Black (BK)
Quantity Per	bag

Product Description	One-piece cable tie and mount offers a simple bundling and mounting solution. The innovative design of this fir tree establishes a 360-degree interface with the panel hole, ensuring a more secure fit. The oval shape won't rotate once inserted, ensuring proper routing of wires and hoses. The disc feature prevents rattling in high-vibration applications and protects against debris ingress.		
Short Description	1-Pc Cable Tie/Fir Tree Mount with Disc, 6.6"L, 6.2 - 13.0 mm, PA66HS, Black, 1000/bag		
Global Part Name	T50SOSFTOVALU-PA66HS-BK		
Minimum Tensile Strength (Imperial)	50.0		
Minimum Tensile Strength (Metric)	225.0		
Length L (Imperial)	6.6		
Length L (Metric)	168.2		
Fixation Method	Fir Tree for oval holes		
Identification Plate Position	none		
Releasable Closure	No		
Tie Closure	plastic pawl		
Variant	Outside Serrated		
Width W (Imperial)	0.20		
Width W (Metric)	5.1		

Bundle Diameter Min (Imperial)	0.08
Bundle Diameter Min (Metric)	2.0
Bundle Diameter Max (Imperial)	1.38
Bundle Diameter Max (Metric)	35.0
Height H (Imperial)	0.51
Height H (Metric)	12.85
Panel Thickness Min (Imperial)	0.023
Panel Thickness Max (Imperial)	0.27
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	6.75
Mounting Hole Diameter D (Imperial)	0.24 x 0.48 ";0.25 x 0.50 ";0.25 x 0.51 ";0.27 x 0.47
Mounting Hole Diameter D (Metric)	6.5 x 12.5 mm 7.0 x 12.0 mm 6.2 x 12.2 mm 6.5 x 13.0 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.51
Mounting Hole Diameter D Max (Metric)	13.0
Disc Diameter (Metric)	17.63 x 23.63
Disc Diameter (Imperial)	0.69 x 0.93

Material	Polyamide 6.6 heat stabilized (PA66HS)
-----------------	--

Material Shortcut	PA66HS
--------------------------	--------

Material Cable Tie	Polyamide 6.6 heat stabilized (PA66HS)
---------------------------	--

Flammability	UL 94 V-2
---------------------	-----------

Operating Temperature	-40°F to +257°F (-40°C to +125°C)
------------------------------	-----------------------------------

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	1000
------------------------------------	------

Package Quantity (Metric)	1000
----------------------------------	------

Customs Number	3926909988
-----------------------	------------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[157-00370](#)