

Kit Description Rev. 1.0 / May 2011









Important Notice

Restrictions in Use

ZMDI's ZLED7020KIT-D1 Demo Kit hardware is designed for ZLED7020 demonstration, evaluation, laboratory setup, and module development only. The ZLED7020KIT-D1 Demo Kit hardware must not be used for module production or production test setups.

Disclaimer

Zentrum Mikroelektronik Dresden AG (ZMD AG) shall not be liable for any damages arising out of defects resulting from

- (i) delivered hard- and software
- (ii) non-observance of instructions contained in this manual and in any other documentation provided to user, or
- (iii) misuse, abuse, use under abnormal conditions or alteration by anyone other than ZMD AG.

To the extent permitted by law, ZMD AG hereby expressly disclaims and user expressly waives any and all warranties, whether express, implied or statutory, including, without limitation, implied warranties of merchantability and of fitness for a particular purpose, statutory warranty of non-infringement and any other warranty that may arise by reason of usage of trade, custom or course of dealing.

Contents

1	Kit	Contents	.3		
2	Kit	Description	.3		
	2.1.	Overview	.3		
	2.2.	Power Supply	.3		
	2.3.	Interface	.4		
	2.4.	Key Demo board features and benefits	.4		
	2.5.	Circuit Operation	.5		
	2.6.	Schematic Diagram	.6		
3	Ord	dering Information	.7		
4	Related Documents7				
5	Glossary7				
6	Do	cument Revision History	.7		

List of Figures

Figure 2.1	ZLED7020KIT-D1 Demo Board (Top View)	4
Figure 2.2	ZLED7020KIT-D1 Schematic Diagram	6

List of Tables

Table 2.1	Table	Fehler!	Textmarke nicht d	efiniert.
-----------	-------	---------	-------------------	-----------

Evoluction Kit	© 2010 Zentrum Mikroelektronik Dresden AG — Rev. 1.0	
Evaluation Kit	All rights reserved. The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without	2 of 7
December 7, 2010	the prior written consent of the copyright owner. The information furnished in this publication is subject to changes without notice.	2017







1 Kit Contents

The ZLED7020KIT-D1 Demo Kit consists of the following parts:

- ZLED7020-D1 Demo Board VX.x
- Five ZLED7020 samples, SOT89-5 package
- ZLED7020KIT-D1 Demo Kit Start-up Information
- Kit Disclaimer

The ZLED7020KIT-D1 Demo Kit is fully assembled and ready for immediate operation.

2 Kit Description

2.1. Overview

The ZLED7020KIT-D1 Demo Kit provides a quick and easy method for evaluating the ZLED7020 within its basic application circuit. Reading the *ZLED7020 Data Sheet* before using the Demo Kit is recommended for understanding the operation of the ZLED7020 and the Demo Board.

The ZLED7020 continuous-mode inductive step-down converter is one of ZLED family of high brightness, high current LED control ICs. It can efficiently drive a single LED or multiple series-connected LEDs from a voltage input higher than the LED voltage (Vin = 6 to 40 VDC). It provides an adjustable output current (1.2A maximum), which is set via an external resistor and controlled by the ZLED7020's integrated high-side output current-sensing circuit. An external control signal (DC voltage or a PWM waveform) on the ADJ pin can be used to linearly adjust the output for either continuous or gated-output current.

The output can be turned off by applying a voltage lower than 0.2V to the ADJ pin, which puts the ZLED7020 in a low-current standby state.

The ZLED7020 IC is designed for LED current drive applications of up to 1.2A. The main features of ZLED7020 driver are:

- Up to 1.2A output current.
- Wide input voltage range: 6V to 40V.
- Internal 40V 1.2A NDMOS switch.
- High efficiency (> 90% possible).
- Up to 1MHz switching frequency.

The Demo Board contains a standard 4-pin terminal connector to allow the user to easily connect and supply a LED's board. The Demo Board also has two LED power pads (LED+ and LED-) to provide more flexibility in supplying a power LED or LED string. A 33uH shielded inductor was chosen to set nominal frequency around 300kHz. The shielded inductor is selected to minimize radiated EMI. The layout with any switching regulator is crucial to minimize radiated EMI. This reference design keeps the critical track lengths to a minimum. Ground has been maximized around critical areas.

Figure 2.1 shows the top view of the populated kit PCB.

2.2. Power Supply

The board requires basically 12V, or above for LED strings, AC or DC power supply. Referring to circuit schematics at Figure 2.2, the shortcut solder joints could be used at R1 and R3, utilizing a zero ohm resistor in order to enable the pure DC operation.

Care has to be taken in this case, since the system is not reverse polarity protected!

Evaluation Kit	\odot 2010 Zentrum Mikroelektronik Dresden AG — Rev. 1.0	
Evaluation Kit	All rights reserved. The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without	3 of 7
December 7, 2010	the prior written consent of the copyright owner. The information furnished in this publication is subject to changes without notice.	0017





The power supply is provided via a standard MR16 connector. In addition, there are two pads for an optional way of supplying the Demo Board.





2.3. Interface

MR16 - Standard male connector for power supply with wide input voltage range 6V to 40V.

VAC 3, 4 – Pads for an optional way of power supply.

CON4 - Standard 2.54mm female header with the following pins:

1, 2 – LED+ Positive pole of the ZLED7020 driver supply voltage.

3, 4 – LED- Negative pole of the ZLED7020 driver supply voltage.

ADJ - puts the ZLED7020 driver in a low current stand-by state.

2.4. Key Demo Board Features and Benefits

- Wide input voltage range.
- Standard 4 pins 2.54mm header for attaching of LEDs and additional duplicate smd pads (LED-, LED+).
- Standard MR16 contact pins and additional duplicate smd pads for power supply.
- Coils footprint designed for various types of coils.
- 3.0mm holes for mounting of an optional heat sink.
- SMD pad for driving of the adjust terminal (ADJ).
- Solder jumpers for by-passing of the bridge rectifier (R1 and R3) in case of usage of an external DC supply.
- All devices SMD and on one side (TOP).
- Maximized power ground copper at top and bottom sides with thermal vias for good heat distribution.
- Easy heat sink attaching option (according to the exploitation conditions demands) at the bottom side.
- Bottom side without solder mask for better thermal contact with heat sink if attached.

Evaluation Kit	© 2010 Zentrum Mikroelektronik Dresden AG — Rev. 1.0 All rights reserved. The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without		
December 7, 2010	the prior written consent of the copyright owner. The information furnished in this publication is subject to changes without notice.	4 01 7	





- Track connecting R2 (current sense resistor) to ZLED7020 as short as possible (being sense tracks).
- The filter capacitor C1 is connected as close as possible to the LED output pins.
- The freewheeling current path is as short as possible to ensure system precision and efficiency.

2.5. Circuit Operation

Circuit operation has been evaluated taking into account maximum output current. The reference current is set to a maximum 1.2A but can be adjusted to any lower value by changing the sense resistor R2 according to the formula:

Iref = 0.1 / R2, [A]

For R2 = 0.082 -> Iref = 1.2A

For detailed calculations, please refer to the ZLED7020 datasheet.

	© 2010 Zentrum Mikroelektronik Dresden AG — Rev. 1.0
Evaluation Kit	All rights reserved. The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without
December 7, 2010	the prior written consent of the copyright owner. The information furnished in this publication is subject to changes without notice.







2.6. Schematic Diagram

Figure 2.2 ZLED7020KIT-D1 Schematic Diagram



© 2010 Zentrum Mikroelektronik Dresden AG — Rev. 1.0

All rights reserved. The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner. The information furnished in this publication is subject to changes without notice.





3 **Ordering Information**

Product Sales Code	Description
ZLED7020KIT-D1	ZLED7020KIT-D1 Demo Kit V1.0 incl. 5 IC samples

Related Documents 4

Document	File Name
ZLED7020 Datasheet	ZLED7020_DataSheet_Rev_X.x.pdf

Visit ZMDI's website www.zmdi.com or contact your nearest sales office for the latest version of these documents.

5 Glossary

Term	Description				
LED	Light Emitted Diode				
MR16	Multifaceted Reflector				
NDMOS	N-type Double-Diffused Metal-Oxide-Semiconductor				
РСВ	Printed Circuit Board				
PWM	Pulse Width Modulation				
SOT89-5	Small Outline Transistor				

Document Revision History 6

Revision	Date	Description
1.0	May 12, 2010	Initial release

Sales and Further Information www.zmdi.com <u>LED drivers@zmdi.com</u>								
Zentrum Mikroelektronik Dresden AG Grenzstrasse 28 01109 Dresden Germany		ZMD America, Inc. 8413 Excelsior Drive Suite 200 Madison, WI 53717 USA		Zentrum Mikroelektronik Dresden AG, Japan Office 2nd Floor, Shinbashi Tokyu Bldg. 4-21-3, Shinbashi, Minato-ku Tokyo, 105-0004 Japan		ZMD FAR EAST, Ltd. 3F, No. 51, Sec. 2, Keelung Road 11052 Taipei Taiwan		
Phone +49 (0)35 Fax +49 (0)35	1.8822.7.533 1.8822.8.7533	Phone Fax	+1 (608) 829-1987 +1 (631) 549-2882	Phone Fax	+81.3.6895.7410 +81.3.6895.7301	Phone - Fax -	⊦886 2 2377 8189 ⊦886 2 2377 8199	
DISCLAIMER: This information applies to a product under development. Its characteristics and specifications are subject to change without notice. Zentrum Mikroelektronik Dresden AG (ZMD AG) assumes no obligation regarding future manufacture unless otherwise agreed to in writing. The information furnished hereby is believed to be true and accurate. However, under no circumstances shall ZMD AG be liable to any customer, licensee, or any other third party for any special, indirect, incidental, or consequential damages of any kind or nature whatsoever arising out of or in any way related to the furnishing, performance, or use of this technical data. ZMD AG hereby expressly disclaims any liability of ZMD AG to any customer, licensee and any other third party hereby waives any liability of ZMD AG for any damages in connection with or arising out of the furnishing, performance or use of this technical data, whether based on contract, warranty, tort (including negligence), strict liability, or otherwise.								
Evaluation Kit © 2010 Zentrum Mikroelektronik Dresden AG — Rev. 1.0 All rights reserved. The material contained herein may not be reproduced, adapted, merged, translated, stored, or used without the prior written consent of the copyright owner. The information furnished in this publication is subject to changes without notice.				7 of 7				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Renesas Electronics: ZLED7020Kit-D1