

Specification Sheet

Part Number: 161-66000



Industry standard blue color assists with visual detection and reduces the risk of contamination.

Included applicator tool makes installation fast and easy.

High stainless-steel content is both detectable and corrosion resistant.

Open design accommodates breakouts at any point along the bundle.

Helawrap Metal-Content, HWPPMC8, .35" Dia, PP/SS, Blue, 82 ft/roll

Article Number	161-66000
----------------	-----------

Type	HWPPMC8
------	---------

Color	Blue (BU)
-------	-----------

Quantity Per	box
--------------	-----

Product Description	Helawrap HWPPMC provides flexible, durable cable and hose protection. It is ideal for food-processing machines and related environments. Protects against abrasion, making it appropriate for applications where movement is an issue. Helawrap is quick and easy to use, making it ideal for installation and maintenance operations.
---------------------	--

Short Description	Helawrap Metal-Content, HWPPMC8, .35" Dia, PP/SS, Blue, 82 ft/roll
-------------------	--

Global Part Name	HWPPMC8-PP/SS-BU
Variant	Spiral Binding
Bundle Diameter Min (Imperial)	0.28
Bundle Diameter Min (Metric)	7
Bundle Diameter Max (Imperial)	0.35
Bundle Diameter Max (Metric)	9
Nominal Diameter (Imperial)	0.31
Nominal Diameter (Metric)	8
Wall Thickness WT (Imperial)	0.030
Wall Thickness WT (Metric)	0.75
Material	Stainless Steel (SS) Polypropylene (PP)
Material Shortcut	PP SS
Flammability	UL 94 HB
Halogen Free	Yes

Operating Temperature	-76°F to +212°F (-60°C to +100°C)
------------------------------	-----------------------------------

Reach Compliant (Article 33)	Yes
-------------------------------------	-----

ROHS Compliant	Yes
-----------------------	-----

Package Quantity (Imperial)	82.0
------------------------------------	------

Package Quantity (Metric)	25
----------------------------------	----

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[161-66000](#)