

Specification Sheet

Part Number: 169-60302

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Convoluted Tubing, Flame Retardant, Slit, 0.25" Dia, PE-FR, Gray, 3200 ft/ctn

| | |
|-----------------------|-----------|
| Article Number | 169-60302 |
|-----------------------|-----------|

| | |
|-------------|----------|
| Type | CTPFR140 |
|-------------|----------|

| | |
|--------------|-----------|
| Color | Gray (GY) |
|--------------|-----------|

| | |
|---------------------|--------|
| Quantity Per | carton |
|---------------------|--------|

| | |
|---------------------------------------|--|
| Product Description | HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires. The Polyethylene flame retardant material provides additional protection that is suitable for applications requiring a self-extinguishing material and complies with UL 94 V2 standards. |
| Short Description | Convoluted Tubing, Flame Retardant, Slit, 0.25" Dia, PE-FR, Gray, 3200 ft/ctn |
| Global Part Name | CTPFR140-PE-FR-GY |
| Length L (Imperial) | 2500.0 |
| Length L (Metric) | 762.0 |
| Variant | Slit |
| Inner Diameter D (Imperial) | 0.276 |
| Inner Diameter D (Metric) | 7.01 |
| Diameter D (Imperial) | 0.398 |
| Diameter D (Metric) | 10.11 |
| Outside Diameter OD (Imperial) | 0.398 |
| Outside Diameter OD (Metric) | 10.11 |

Nominal Diameter (Imperial) 0.25

Nominal Diameter (Metric) 6.35

Wall Thickness WT (Imperial) 0.004

Wall Thickness WT (Metric) 0.102

Material Polyethylene, flame retardant (PE-FR)

Material Shortcut PE-FR

Flammability UL 94 V-2

Halogen Free No

Operating Temperature -40°F to +185°F (-40°C to +85°C)

Reach Compliant (Article 33) Yes

ROHS Compliant Yes

Package Quantity (Imperial) 3200

Package Quantity (Metric) 762.0

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[169-60302](#)