

Specification Sheet

Part Number: 169-60533

Split side is ideal for applications where braided tubing or spiral wrap may be difficult to install.

Tubing provides full coverage where spiral wrap or other coverings may not be suitable.

In harsh applications the tubing provides resistance to crushing, impact, and abrasion.

Tubing offers excellent protection against automotive fluids, vibration wear, water, snow, ice, and the effects of heat, cold, and sunlight on cables and wires.



Article Number	169-60533
Type	CTP340
Color	Red (RD)
Quantity Per	carton

Product Description	<p>HellermannTyton's Convoluted Tubing, also known as Split Loom Tubing, provides an efficient method of routing and protecting wire harness assemblies, while reducing the chance of installation damage. With a split down the side where you can insert your wire harness, you can just easily install Convoluted Tubing without removal of the entire assembly. It can also serve to protect valuable hoses and cables. Convoluted tubing offers excellent protection against vibration wear, water, snow, ice and the effects of heat, cold and sunlight on cables and wires.</p>
Short Description	Convoluted Tubing, Slit, 0.75" Dia, PE, Red, 550 ft/carton
Global Part Name	CTP340-PE-RD
Length L (Imperial)	550.0
Length L (Metric)	167.6
Inner Diameter D (Imperial)	0.759
Inner Diameter D (Metric)	19.28
Diameter D (Imperial)	0.989
Diameter D (Metric)	25.12
Outside Diameter OD (Imperial)	0.989
Outside Diameter OD (Metric)	25.12
Nominal Diameter (Imperial)	0.75
Nominal Diameter (Metric)	19.05

Wall Thickness WT (Imperial)	.005
Wall Thickness WT (Metric)	0.127
Material	Polyethylene (PE)
Material Shortcut	PE
Halogen Free	No
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +199°F (-40°C to +93°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	550
Package Quantity (Metric)	167.60
Customs Number	3926909988



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[169-60533](#)