

Specification Sheet

Part Number: TSRP1I-8A

Tamper resistant covers with hidden latch provide security while allowing quick entry for cable maintenance.

U.L. Listed for power up to 600 Volts, meeting UL5A and CSA 22.2 Number 62-93 Standards.

Manufactured from UL 94V-0 rated PVC material.

Fittings incorporate a minimum 1" bend radius per TIA/EIA 568-B and 569-A standards.

Large base for greater adhesive surface.

Rubber-based foam tape adhesive with high ultimate bond strength, which conforms to any surface.

Flexible hinge allows the raceway to endure numerous openings without creating discoloration or stress cracking.

Junction boxes can be used for electrical or data outlets.

Designed to complement HellermannTyton's industry standard TSR low voltage raceway system.



One Piece Power Rated Raceway, 3/4", 8.0 ft Long, PVC, Ivory, 160ft/Carton

Article Number 250-61801

Type TSRP1-8A

Color Ivory (IV)

Quantity Per	carton
Product Description	HellermannTyton surface raceway systems are the ideal solution for routing communication and power cables. No need to break into existing walls - raceway systems are designed to route cable along wall surfaces. Made of a PVC material, components are durable and affordable; and the one piece construction and adhesive tape backing make positioning and mounting easy. HellermannTyton offers a low voltage TSR system and a power rated TSRP system that are available in three different diameters to accommodate different cable and wire bundle and conduit sizes. Both systems include a complete line of fittings and junction boxes that allow for clean and professional installations. TSRP surface raceway systems are designed to aesthetically organize and route either power or communications cables.
Short Description	One Piece Power Rated Raceway, 3/4", 8.0 ft Long, PVC, Ivory, 160ft/Carton
Global Part Name	TSRP1-8A-PVC-BGE
Length L (Imperial)	8.0
Length L (Metric)	2.44
Width W (Imperial)	0.75
Width W (Metric)	19.05
Height H (Imperial)	.50
Height H (Metric)	12.70

Material	Polyvinylchloride (PVC)
----------	-------------------------

Material Shortcut	PVC
-------------------	-----

Flammability	UL 94 V-0
--------------	-----------

Halogen Free	No
--------------	----

UV Resistant (Yes/No)	No
-----------------------	----

Use Conditions	For Indoor Use Only
----------------	---------------------

Operating Temperature	+122°F (+50°C)
-----------------------	----------------

Reach Compliant (Article 33)	No
------------------------------	----

ROHS Compliant	Yes
----------------	-----

UL Listed (US and Canada)	Yes
---------------------------	-----

UL Listed (US)	Yes
----------------	-----

Package Quantity (Imperial)	160.0
-----------------------------	-------

Package Quantity (Metric)	48.80
---------------------------	-------

Customs Number	3925900000
----------------	------------

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[TSRP1I-8A](#)