


## Specification Sheet

Part Number: 553-50004

Slide Slit and optional center slits for easy wire insertion.  
Smooth surface for clean and legible printing.

Supplied on a ladder style carrier so that markers can be kitted after printing.



A 3:1 shrink ratio means fewer skews as each marker covers a wider range of wire diameters.

ShrinkTrak Labels, 1-Sided, 1-Slit, .125" (3.17mm), PO-X, White, 500/box

|                       |           |
|-----------------------|-----------|
| <b>Article Number</b> | 553-50004 |
|-----------------------|-----------|

|             |            |
|-------------|------------|
| <b>Type</b> | HST3-1WH-S |
|-------------|------------|

|              |            |
|--------------|------------|
| <b>Color</b> | White (WH) |
|--------------|------------|

|                     |     |
|---------------------|-----|
| <b>Quantity Per</b> | box |
|---------------------|-----|

|                            |                                                                                                                                                                                                                                                                                                                                                                                                                       |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Product Description</b> | HellermannTyton's ShrinkTrak heat shrinkable markers make it easy to mark wire, cable and other components. The military approved heat shrink tubing is flattened and assembled in a ladder style carrier system for easy printing using a thermal transfer printer. The ladder system creates a kit of markers that can be sorted, removed and applied in any order thus saving time, labor and speeding production. |
|----------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|

|                          |                                                                          |
|--------------------------|--------------------------------------------------------------------------|
| <b>Short Description</b> | ShrinkTrak Labels, 1-Sided, 1-Slit, .125" (3.17mm), PO-X, White, 500/box |
|--------------------------|--------------------------------------------------------------------------|

|                         |                    |
|-------------------------|--------------------|
| <b>Global Part Name</b> | HST3-1WH-S-PO-X-WH |
|-------------------------|--------------------|

|                |           |
|----------------|-----------|
| <b>Variant</b> | Thin-Wall |
|----------------|-----------|

|                           |      |
|---------------------------|------|
| <b>Width W (Imperial)</b> | 0.95 |
|---------------------------|------|

|                         |       |
|-------------------------|-------|
| <b>Width W (Metric)</b> | 24.13 |
|-------------------------|-------|

|                               |      |
|-------------------------------|------|
| <b>Thickness T (Imperial)</b> | .003 |
|-------------------------------|------|

|                             |       |
|-----------------------------|-------|
| <b>Thickness T (Metric)</b> | .0762 |
|-----------------------------|-------|

|                            |       |
|----------------------------|-------|
| <b>Height H (Imperial)</b> | 0.235 |
|----------------------------|-------|

|                          |      |
|--------------------------|------|
| <b>Height H (Metric)</b> | 5.69 |
|--------------------------|------|

|                                |      |
|--------------------------------|------|
| <b>Width of Liner (Metric)</b> | 76.2 |
|--------------------------------|------|

|                                  |     |
|----------------------------------|-----|
| <b>Width of Liner (Imperial)</b> | 3.0 |
|----------------------------------|-----|

|                                       |       |
|---------------------------------------|-------|
| <b>Outside Diameter OD (Imperial)</b> | 0.125 |
|---------------------------------------|-------|

|                                     |     |
|-------------------------------------|-----|
| <b>Outside Diameter OD (Metric)</b> | 3.2 |
|-------------------------------------|-----|

|                                        |       |
|----------------------------------------|-------|
| <b>Outside Diameter Max (Imperial)</b> | 0.125 |
|----------------------------------------|-------|

|                                      |     |
|--------------------------------------|-----|
| <b>Outside Diameter Max (Metric)</b> | 3.2 |
|--------------------------------------|-----|

|                                     |       |
|-------------------------------------|-------|
| <b>Wall Thickness WT (Imperial)</b> | 0.031 |
|-------------------------------------|-------|

|                                   |      |
|-----------------------------------|------|
| <b>Wall Thickness WT (Metric)</b> | 0.79 |
|-----------------------------------|------|

|                                     |                                                                              |
|-------------------------------------|------------------------------------------------------------------------------|
| <b>Material</b>                     | Polyolefin, cross-linked (PO-X)                                              |
| <b>Material Shortcut</b>            | PO-X                                                                         |
| <b>US MIL SPEC</b>                  | SAE-AS81531<br>MIL-STD-202G Method 215K<br>SAE-AMS-DTL-23053/5 Class 1 and 3 |
| <b>Flammability</b>                 | UL 224 VW-1                                                                  |
| <b>Halogen Free</b>                 | No                                                                           |
| <b>Operating Temperature</b>        | -67°F to +275°F (-55°C to +135°C)                                            |
| <b>Reach Compliant (Article 33)</b> | Yes                                                                          |
| <b>ROHS Compliant</b>               | Yes                                                                          |
| <b>Certification/Specification</b>  | UL 224 125 °C 600V VW-1                                                      |
| <b>Package Quantity (Imperial)</b>  | 500                                                                          |
| <b>Package Quantity (Metric)</b>    | 500                                                                          |
| <b>Customs Number</b>               | 3917320000                                                                   |
| <b>Labels per Column</b>            | 1                                                                            |
| <b>Labels per Row</b>               | 2                                                                            |

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[553-50004](#)