


Specification Sheet

Part Number: 596-00496

Pre-Printed Vinyl Solar Labels are made with UV-stable inks and materials for durability and weather resistance.
Supplied with an aggressive adhesive to ensure long life.

Meets NEC & IFC standards for printed text, character height, color and outdoor UV stability to pass inspections.

Pre-printed labels offer significant time and cost savings over high priced plastic engraved phenolic placards and lead time purchased markers.



Article Number	596-00496
Type	WESHLBLDC
Color	Orange (OG)
Quantity Per	roll
Product Description	HellermannTyton pre-printed Solar Installation Labels are designed to meet the requirements of the National Electrical Code and the International Fire Code as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV-stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer when variable voltage or series data must be printed and displayed.

Short Description	Solar Label, WARNING ELECTRICAL SHOCK HAZARD...DC VOLTAGE, 3.75" x 2.5", VL, Orange/White, 50/roll
Global Part Name	WESHLBLDC-443/281-OG
Technical Description	Pre-Printed Solar Label, "WARNING - ELECTRICAL SHOCK HAZARD W/DC", 3.75" X 2.5", Orange/White
Local Order Number 2	Cross Reference = 10 per pack: 596-00661; Metal Solar Placard 5 pack: 596-00829; Spanish Version 50 per roll: 596-00802
Length L (Imperial)	2.5
Length L (Metric)	63.5
Width W (Imperial)	3.75
Width W (Metric)	95.25
Thickness T (Imperial)	0.0025
Thickness T (Metric)	64.0
Height H (Imperial)	2.50
Height H (Metric)	63.5
Material	Type 443/281, UV-stabilized flexible white vinyl with clear polyester laminate (443/281)

Material Shortcut	443/281
Adhesive	Acrylic
Halogen Free	No
Adhesive Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Operating Temperature	-40°F to +174°F (-40°C to +79°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	UL 969 NEC2014
Warranty (US)	Yes
UL Recognized (US)	Yes
Package Quantity (Imperial)	50
Package Quantity (Metric)	50
Customs Number	3919102055
Labels per Column	1
Labels per Row	1

© 2022 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00496](#)