


Specification Sheet

Part Number: 596-00864

Placards made with UV stable inks and materials tested to last up to 25 years, even in direct sun exposure.
Aggressive adhesive ensures strong bond, even on powder coated surfaces.
Meets or exceeds NEC & IFC standards for printed text, character height, color and outdoor UV stability.

Optional Paint Shields provide additional protection for pre-printed and variable data placards.



Metal Solar Placard, Hand Writable, DC Rating Label, 4.0" x 2.0", AA, Black, 5/pkg

Article Number	596-00864
Type	DCRATINGM5
Color	Black (BK)
Quantity Per	pcs.
Product Description	Variable data placards are used to mark areas specific to the individual installation, like voltage data. Made of the same durable material as pre-printed metal solar placards, hand-writable placards are designed to meet industry codes. Hand-writable placards feature a silver variable data area that can be marked using an industrial paint pen.

Short Description	Metal Solar Placard, Hand Writable, DC Rating Label, 4.0" x 2.0", AA, Black, 5/pkg
Global Part Name	DCRATINGM5-AA-BK
Technical Description	Pre-Printed Metal Solar Placard, 2008 DC Rating Label for printing", 4.0" X 2.00", Black
Local Order Number 2	Cross Reference = Paint Shield: 596-00794
Length L (Imperial)	2.00
Length L (Metric)	50.8
Width W (Imperial)	4.0
Width W (Metric)	101.6
Height H (Imperial)	2.0
Height H (Metric)	50.80
Material	Anodized Aluminum (AA)
Material Shortcut	AA
Adhesive	Ultra High Bond Permanent Acrylic Adhesive
Halogen Free	No

Adhesive Operating Temperature	from +50°F (from +10°C)
Operating Temperature	-40°F to +203°F (-40°C to +95°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Certification/Specification	NEC2014
Warranty (US)	Yes
Package Quantity (Imperial)	5
Package Quantity (Metric)	5
Customs Number	3919905060
Labels per Column	1
Labels per Row	1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HellermannTyton:](#)

[596-00864](#)