

CT2131

Banana Plug Test Lead, Silicone

4 mm Stacking Banana Plug to Stacking Banana Plug Test...

Description

4 mm Stacking Banana Plug to Stacking Banana Plug Test Lead. Highly flexible Silicone lead w. Lead for all applications. Stacking feature allows for multiple connections.

- Materials: Body: Polyamide (Nylon); Contact: Brass, Nickel Plt.
- Banana Contact: BeCu, Nickel Plt.
- Available in 6 standard lengths



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com

Datasheet



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

IEC Rating	33 V AC / 70 V DC
Voltage, Max	1,200 V AC/DC
Current, Max	12 A
Resistance, Max	55 milliohms
Jacket Material	Silicone
Conductor Area	0.75 mm ²
Wire Gauge	18 AWG
Stranding (# x dia.)	195 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Cal Test Electronics:

[CT2131-10-0](#) [CT2131-10-2](#) [CT2131-10-4](#) [CT2131-10-5](#) [CT2131-10-6](#) [CT2131-10-9](#) [CT2131-50-6](#) [CT2131-50-9](#)
[CT2131-25-4](#) [CT2131-25-5](#) [CT2131-25-6](#) [CT2131-25-9](#) [CT2131-50-4](#) [CT2131-50-5](#) [CT2131-150-6](#) [CT2131-150-9](#)
[CT2131-200-4](#) [CT2131-200-5](#) [CT2131-200-6](#) [CT2131-200-9](#) [CT2131-100-4](#) [CT2131-100-5](#) [CT2131-100-6](#) [CT2131-100-9](#) [CT2131-150-4](#) [CT2131-150-5](#)