



THIS IS ISSUED IN STRICT CONFIDENCE THAT IT IS NOT USED AS A BASIS FOR MANUFACTURE OR SALE AND THAT IT IS NOT COPIED, REPRINTED OR DISCLOSED TO A THIRD PARTY EITHER WHOLLY OR IN PART WITHOUT THE PRIOR WRITTEN CONSENT OF CAL TEST ELECTRONICS, INC.

REVISIONS			
REV.	DESCRIPTIONS	DATE	APPROVED
—	CLASS A RELEASED	7/12/99	

1. 4mm UNINSULATED SOCKET (JACK) w/Ø .080 (Ø 2.0)  
SOLDER HOLE.
2. SPECIFICATIONS:  
SOCKET BODY: BRASS, NICKEL PLATED.
3. RATING:  
CURRENT: 36A MAX.  
TEMPERATURE: -20° C TO +150° C.
4. MOUNTING HOLE: REFERENCE DIAGRAM.
5. MAXIMUM PANEL THICKNESS: .50 (12.7)

PART NUMBER  
GT2220



<b>THIRD ANGLE PROJECTION</b>		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS    DECIMALS $\pm 1/32$ $.XX \pm .02$ $.XXX \pm .005$ DO NOT SCALE DRAWING	CONTRACT NO.		Cal Test Electronics 22820 Savi Ranch Parkway Yorba Linda, CA 92887-4610				
			APPROVALS	DATE					
		DRAWN	WDH	TITLE					
		CHECKED		4mm SOCKET, UNINSULATED					
		FINISH	ENGR.	SIZE <b>A</b>	CAGE CODE		DWG. NO.	REV. —	
NEXT ASSY	USED ON		DESIGN ACTIVITY				P222000		
APPLICATION				SCALE	1:1			SHEET	1 OF 1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT2220](#)