




THIS IS ISSUED IN STRICT CONFIDENCE
THAT IT IS NOT USED AS A BASIS FOR
MANUFACTURE OR SALE AND THAT IT IS
NOT COPIED, REPRINTED OR
DISCLOSED TO A THIRD PARTY EITHER
WHOLLY OR IN PART WITHOUT THE
PRIOR WRITTEN CONSENT OF CAL TEST
ELECTRONICS, INC.

NOTES:

1. ALL SPECIFICATIONS SUBJECT TO CHANGE WITHOUT NOTICE
2. MATERIAL:
 - MDP CONNECTOR -
 - MOLDED BODY: POLYPROPYLENE (PP), BLACK.
 - 4mm BANANA PLUGS -
 - BODY: BRASS, NICKEL PLT.
 - CAGE CONTACT: BECU, NICKEL PLT.
 - RG58C/U COAX CABLE -
 - JACKET: PVC, BLACK; ϕ 4.95 O.D.
 - DIELECTRIC: PE
 - CENTER CONDUCTOR: 22 AWG (19X34) TINNED COPPER, STRANDED.
 - BNC MALE CONNECTOR -
 - BODY & COUPLING NUT: BRASS, NICKEL PLT.
 - DIELECTRIC: PTFE
 - CENTER CONTACT: BRASS, GOLD PLT.
 - MOLDED BOOT: PVC, BLACK
3. ELECTRICAL:
 - IMPEDANCE:
 - ASSEMBLY: NON-CONSTANT
 - BNC & RG58C/U: 50 Ω
 - VOLTAGE -
 - 30 VRMS / 60 VDC (HANDHELD)
 - 500 VRMS (HANDS FREE)
 - DO NOT USE ON CIRCUITS SUBJECT TO TRANSIENT OVERVOLTAGES.
 - CURRENT: 3 A MAX.
4. MECHANICAL:
 - OPERATING TEMPERATURE: 0°C TO +50°C
 - CABLE BEND RADIUS:
 - REPEATED MIN. - 49.8 mm
 - ONE-TIME MIN. - 25 mm
5. CE MARKED
 - ROHS 2 COMPLIANT.



SCHEMATIC

THIRD ANGLE PROJECTION	<div>UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ARE: X.X = ±0.5 X.X* = ±0.5* X.XX = ±0.25 X.XXX = ±0.125 DO NOT SCALE DRAWING</div> <div>MATERIAL SEE NOTES</div>	PROJECT NO. A660(a)		METRIC		<div>Cal Test ELECTRONICS</div> <div>22820 Savi Ranch Prky. Yorba Linda, CA 92887 USA</div>		
<div></div>		APPROVALS	DATE	TITLE CABLE ASSEMBLY, MDP TO BNC MALE, RG58C/U				
		DRAWN WDH	6/2/2021					
		CHECKER						
	TREATMENT N/A	ENGR. B. HANSEN	6/3/2021	SIZE B	CAGE CODE 43F45	DWG. NO. CT4450		REV. D
	FINISH N/A	DESIGN ACTIVITY ENGINEERING	6/2/2021	SCALE 1:1		SHEET 1 OF 1		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Cal Test Electronics:](#)

[CT4450-100](#)