


RF_35/09.14/6.2 Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG

Technical Data Sheet		Rosenberger																						
RPC-2.92	Calibration Kit Plug	02S30R-MSOS3																						
																								
All dimensions are in mm; tolerances according to ISO 2768 m-H																								
Interface		IEC 61169-35 RPC-3.50 and SMA																						
Contents and Documentation		This kit is delivered with • Standard Definitions Card Printed Standard Definitions that can be used on nearly all Vector Network Analyzers • Test Results Documentation • Hard Shell Case • Protection Caps																						
Material and plating		<table><tr><td>Connector parts</td><td>Material</td><td>Plating</td></tr><tr><td>Center conductor</td><td>CuBe</td><td>Gold, min. 1.27 µm, over nickel</td></tr><tr><td>Outer conductor</td><td>Stainless steel</td><td>Passivated</td></tr><tr><td>Coupling nut</td><td>Stainless steel</td><td>Passivated</td></tr><tr><td>Body</td><td>Aluminum</td><td>black anodized</td></tr><tr><td>Dielectric</td><td>PS</td><td></td></tr><tr><td>Substrate</td><td>Al₂O₃</td><td></td></tr></table>		Connector parts	Material	Plating	Center conductor	CuBe	Gold, min. 1.27 µm, over nickel	Outer conductor	Stainless steel	Passivated	Coupling nut	Stainless steel	Passivated	Body	Aluminum	black anodized	Dielectric	PS		Substrate	Al ₂ O ₃	
Connector parts	Material	Plating																						
Center conductor	CuBe	Gold, min. 1.27 µm, over nickel																						
Outer conductor	Stainless steel	Passivated																						
Coupling nut	Stainless steel	Passivated																						
Body	Aluminum	black anodized																						
Dielectric	PS																							
Substrate	Al ₂ O ₃																							
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de		Tel. : +49 8684 18-0 Email : info@rosenberger.de																						
		Page 1 / 3																						

Technical Data Sheet		Rosenberger	
RPC-2.92	Calibration Kit Plug	02S30R-MSOS3	
Electrical data Frequency rangeDC to 40.0 GHz OpenError from nominal phase¹ ≤ 1.5°, DC to 4 GHz ≤ 4.0°, 4 GHz to 26.5 GHz ≤ 5.0°, 26.5 GHz to 40.0 GHz ShortError from nominal phase² ≤ 1.5°, DC to 4 GHz ≤ 4.0°, 4 GHz to 26.5 GHz ≤ 5.0°, 26.5 GHz to 40.0 GHz LoadReturn loss ≥ 40.0 dB, DC to 4 GHz ≥ 28.0 dB, 4 GHz to 26.5 GHz ≥ 25.0 dB, 26.5 GHz to 40.0 GHz DC Resistance50 Ω ± 0.5 Ω Power handling (at 25 °C, sea level)≤ 0.5 W, derate by 0.005 W/K ¹ The nominal phase is defined by the Offset Delay, the Offset Loss and the Fringing Capacitances ² The nominal phase is defined by the Offset Delay, the Offset Loss and the Short Inductance			
Mechanical data Mating cycles≥ 500 Maximum torque1.70 Nm Recommended torque0.90 Nm Gauge0.00 mm to 0.08 mm			
General standard definitions For proper operation the vector network analyzer (VNA) needs a model describing the electrical behaviour of this calibration standard. The different models, units, and terms used will depend on the VNA type and they will have to be entered into the VNA. All values are based on typical geometry and plating. Open Offset Z_o / Impedance / Z_o50 Ω Offset Delay28.353 ps Length (electrical) / Offset Length8.50 mm Offset Loss2.40 GΩ/s Loss0.0118 dB/√GHz Fringing Capacitances C₀ = -7.38000 x 10⁻¹⁵ F / -7.38000 fF C₁ = 1180.00 x 10⁻²⁷ F/Hz / 1.18000 fF /GHz C₂ = -44.8000 x 10⁻³⁶ F/Hz² / -0.04480 fF /GHz² C₃ = 0.54000 x 10⁻⁴⁵ F/Hz³ / 0.00054 fF /GHz³			
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de		Tel. : +49 8684 18-0 Email : info@rosenberger.de	Page 2 / 3

Technical Data Sheet				Rosenberger			
RPC-2.92		Calibration Kit Plug		02S30R-MSOS3			
Short Offset Z_o / Impedance / Z_o50 Ω Offset Delay28.353 ps Length (electrical) / Offset Length8.50 mm Offset Loss2.40 GΩ/s Loss0.0118 dB/√GHz Short InductanceL₀ = 0.0000 x 10⁻¹² H / 0.0000 pH L₁ = 0.0000 x 10⁻²⁴ H/Hz / 0.0000 pH/GHz L₂ = 0.0000 x 10⁻³³ H/Hz² / 0.0000 pH/GHz² L₃ = 0.0000 x 10⁻⁴² H/Hz³ / 0.0000 pH/GHz³ Load Offset Z_o / Impedance / Z_o50 Ω Offset Delay0.0000 ps Length (electrical) / Offset Length0.000 mm Offset Loss0.00 GΩ/s Loss0.0000 dB/√GHz Environmental data Operating temperature range³+20 °C to +26 °C Rated temperature range of use⁴0 °C to +50 °C Storage temperature range-40 °C to +85 °C RoHScompliant ³ Temperature range over which these specifications are valid. ⁴ This range is underneath and above the operating temperature range, within the calibration kit is fully functional and could be used without damage Declaration of documentation Standard delivery for this kit includes Test Results. The documentation issued reports which quantities were tested individually, traceable to national / international standards. Model based standard definitions of the calibration standards are reported in Agilent / Keysight, Rohde & Schwarz and Anritsu compatible VNA format. Inspection interval Recommendation12 months Packing Standard1 pce in bag Weight29 g/pce While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Marcel Panicke	05.11.15	Markus Müller	07.05.20	f00	20-1038	Marion Striegler	08.05.20
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 3 / 3

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[02S30R-MSOS3](#)