



Contents

| Device | Part number | QTY | Calibration Option ^a |
|--|-----------------|-----|---------------------------------|
| 20 dB Attenuator plug/jack | 05AS122-K20S3 | 1 | FC |
| 40 dB Attenuator plug/jack | 05AS122-K40S3 | 1 | FC |
| Mismatch Airline plug/jack | 05S102-K100 | 1 | FC |
| Including 50 Ω Center Conductor | 05S101-K100/20D | 1 | |
| Combi wrench | 53W011-000 | 1 | - |

a. See "Declaration of calibration options" for explanation.

This Verification Kit is designed as an electrical verification standard. Reference measurement values (calibration results) for transmission and reflection are included. Connected to a calibrated VNA the actual measured transmission and reflection values can be compared to the reference measurement values and the quality of the VNA calibration can be evaluated.

Documentation

This kit is delivered with

- **USB-Stick**
With S2p data file of the reference measurement values. Calibration Certificate as PDF-file.
- **Kit Info Card**
Handling precautions.
- **Calibration Certificate**
Details see "Declaration of calibration options".
- **Operating Manual**

Electrical specifications

This specification covers electrical key values for the main items of the verification kit. Specific datasheets are available for each component among the part number.

| Device | Frequency | Parameter | Specification |
|---|--|---|--|
| 20 dB Attenuator | DC to ≤ 4 GHz > 4 GHz to ≤ 18 GHz DC to ≤ 4 GHz > 4 GHz to ≤ 18 GHz | Return Loss Return Loss Insertion Loss Insertion Loss | ≥ 32 dB ≥ 26 dB 20 dB \pm 0.30 dB 20 dB \pm 0.50 dB |
| 40 dB Attenuator | DC to ≤ 4 GHz > 4 GHz to ≤ 18 GHz DC to ≤ 4 GHz > 4 GHz to ≤ 18 GHz | Return Loss Return Loss Insertion Loss Insertion Loss | ≥ 32 dB ≥ 23 dB 40 dB \pm 0.50 dB 40 dB \pm 1.00 dB |
| 25 Ω Mismatch Airline | | Outer conductor: Diameter Length Center Conductor: Diameter 50 Ω section Diameter 25 Ω section Length total Length 25 Ω section | 7.000 mm nominal 100.00 mm nominal 3.040 mm nominal 4.615 mm nominal 100.00 mm nominal 75.00 mm nominal |
| 50 Ω Airline Center Conductor | | Diameter Length | 3.040 mm nominal 100.00 mm nominal |

| | | |
|----------------------|------------------|--------------------|
| Technical Data Sheet | | Rosenberger |
| RPC-N 50 Ω | Verification Kit | 05CK050-150 |

Declaration of calibration options

Factory Calibration

Standard delivery for this verification standard includes a Factory Calibration. The Calibration Certificate issued reports individual calibration results, traceable to national / international standards. A S2p data file with the reference measurement values is included.

Accredited Calibration

Optional this kit can be delivered with an Accredited Calibration (DAkkS) having the highest confidence in the traceability. The DAkkS Calibration Certificate issued reports individual transmission and reflection calibration results traceable to national / international standards. S2p data files with reference measurement values and measurement uncertainties in electronic format are included for each Attenuator. The measurement uncertainties are smaller than in a Factory Calibration.

For further, more detailed information see application note AN001 on the Rosenberger homepage.

Calibration interval

Recommendation 12 months

Recommended accessories

- Rosenberger Test Port Adaptor
- Rosenberger Gauge Kit 05GK0KS-010
- Rosenberger VNA Test cable kit and Microwave Cable Assemblies

For further, more detailed information please visit our homepage www.rosenberger.com.

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

| Draft | Date | Approved | Date | Rev. | Engineering change number | Name | Date |
|--|----------|--------------|----------|------|---|-------|-------------------|
| F. Reiner | 17.12.18 | Martin Moder | 04.12.19 | b01 | 19-2230 | M.Ruf | 04.12.19 |
| Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de | | | | | Tel. : +49 8684 18-0 Fax : +49 8684 18-499 Email : info@rosenberger.de | | Page 3 / 3 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[05CK050-150](#)