



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

RPC-N according to
RPC-SL

IEC 60169-16 ; CECC 22 210 ; MIL-STD 348A/402
Interchangeable port connector system

Documents

N/A

Material and plating

Connector parts

- Center contact
- Outer contact RPC-N
- Outer contact RPC-SL
- Coupling nut
- Dielectric

Material

- Beryllium copper
- Stainless steel
- Stainless steel
- Stainless steel
- PPE

Plating

- Gold, min. 1.27 µm, over chemical nickel
- Passivated
- Gold, 0.1 µm min.
- Passivated

**ADAPTOR
RPC-N 50 Ω JACK – RPC-SL PLUG**

05K104-S00S3

Electrical data

Impedance	50 Ω
Frequency	DC to 18 GHz
Return loss	≥ 21 dB, DC to 18 GHz
Insertion loss	≤ 0.05 x √f(GHz) dB
Insulation resistance	≥ 5 GΩ
Center contact resistance RPC-N	≤ 1.0 mΩ
Outer contact resistance RPC-N	≤ 1.0 mΩ
Center contact resistance RPC-SL	≤ 3.0 mΩ
Outer contact resistance RPC-SL	≤ 2.0 mΩ
Test voltage	1000 V rms
Working voltage	335 V rms
RF-leakage	≥ 90 dB up to 1 GHz

Mechanical data

Mating cycles RPC-N	≥ 500
Mating cycles RPC-SL	≥ 3000
Center contact captivation	≥ 28 N
Coupling test torque RPC-N	1.70 Nm
Recommended torque RPC-N	0.70 Nm to 1.10 Nm
Recommended torque RPC-SL	2 Nm

Environmental data

Temperature range	-40°C to +85°C
Thermal shock	IEC 61169-1, Subclause 9.4.4
Corrosion	IEC 61169-1, Subclause 9.4.6
Vibration	IEC 61169-1, Subclause 9.3.3
Shock	IEC 61169-1, Subclause 9.3.14
Moisture resistance 2002/95/EC (RoHS)	IEC 61169-1, Subclause 9.4.3 compliant

Tooling

N/A

Suitable cables

N/A

Packing

Standard	1 pce in box
Weight	33.0 g/pce

While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.

Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	26/07/04	H. Babinger	08.02.07	c00	07-0101	B. Dandl	17/10/06

Rosenberger Hochfrequenztechnik GmbH & Co. KG
P.O.Box 1260 D-84526 Tittmoning Germany
www.rosenberger.de

Tel.: +49 8684 18-0
Fax: +49 8684 18-499
email: info@rosenberger.de

Page
2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[05K104-S00S3](#)