



All dimensions are in mm; tolerances according to ISO 2768 m-H

## Interface

According to IEC 61169-16

## Documents

Application note AN001 "Calibration Services"

## Material and plating

### Connector parts

Center conductor  
Outer conductor  
Dielectric  
Substrate

### Material

CuBe  
Stainless steel  
PPE  
Al<sub>2</sub>O<sub>3</sub>

### Plating

Gold, min. 1.27 µm, over nickel  
Passivated

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG  
RF\_35/09:14/6.2

Technical Data Sheet				Rosenberger			
RPC-N		Mismatch Jack		05K150-060S3			
<b>Electrical data</b>							
Frequency range		DC to 18 GHz					
VSWR		1.2 ± 0.04, DC to 8 GHz					
		1.2 ± 0.05, 8 GHz to 12.4 GHz					
		1.2 ± 0.07, 12.4 GHz to 18 GHz					
DC Resistance		60 Ω					
Power handling		≤ 1 W					
<b>Mechanical data</b>							
Mating cycles		≥ 500					
Maximum torque		1.70 Nm					
Recommended torque		1.10 Nm					
Gauge		5.18 mm to 5.26 mm					
<b>Environmental data</b>							
Operating temperature range <sup>1</sup>		+20 °C to +26 °C					
Rated temperature range of use <sup>2</sup>		0 °C to +50 °C					
Storage temperature range		-40 °C to +85 °C					
RoHS		compliant					
<sup>1</sup> Temperature range over which these specification are valid.							
<sup>2</sup> This range is underneath and above the operating temperature range, within the mismatch is fully functional and could be used without damage.							
<b>Declaration of calibration options</b>							
<b>Factory Calibration</b>							
Standard delivery for this calibration standard includes a Factory Calibration. The Calibration Certificate issued reports individual calibration results, traceable to national / international standards.							
<b>Accredited Calibration</b>							
Optional this calibration standard can be delivered with an Accredited Calibration (DAkkS) having the highest confidence in the traceability. The DAkkS Calibration Certificate issued reports individual calibration results in a complex format, traceable to national / international standards. Calibration results are reported in a dense data set file. The uncertainties are smaller than in a Factory Calibration.							
For further, more detailed information see application note AN001 on the Rosenberger homepage.							
<b>Calibration interval</b>							
Recommendation		12 months					
<b>Packing</b>							
Standard		1 pce in box					
Weight		41.8 g/pce					
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Kerstin Herzog	12.07.04	Martin Moder	29.01.15	e00	14-1492	Herbert Babinger	29.01.15
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page  2 / 2	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[05K150-060S3](#)