



M12 Cable Set Series

Cables for sensors with M12 round connection



- 4 pole M12 connector to IEC61076-2-101
- IP67 protection IEC 60529 (a3)
- Anti-vibration system
- Head temperature range -40 90°C, with good resistance to oils
- Choice of PVC or PUR/PVC cable insulation

Technical Specification

Protection degree IEC 60529 (a3)	IP67
Head temperature range °C	-40 to 90
Cable temperature range °C	PVC -25 to 90 PUR -25 to 80
Housing oil resistance	very good
Housing material	TPU (polyurethane)
Contact material	Gold over nickel plated CuZn
Locking nut material	Nickel plated Brass
Conductor size	4/0.34 mm ²

Electrical Specification

Voltage AC Max	V	250
Voltage DC Max	V	250
Current Max @40°C	A	4
Voltage drop @1A x 1M	V	0.13




The LC cable series can be used with sensors that have M12 round connectors (IEC61076-2-101).

These are supplied as standard with choice of PVC or PUR/PVC sheath insulated cables in lengths of 2, 5 and 10 metres and with either straight or elbow connector bodies.

Standard Parts	Cable sheath	Wire insulation	Wire cores	Body type	Length (m)
LC02FBS-PVC	PVC	PVC	4/0.34	Straight	2
LC05FBS-PVC	PVC	PVC	4/0.34	Straight	5
LC10FBS-PVC	PVC	PVC	4/0.34	Straight	10
LC02FBS-PUR	PUR	PVC	4/0.34	Straight	2
LC05FBS-PUR	PUR	PVC	4/0.34	Straight	5
LC10FBS-PUR	PUR	PVC	4/0.34	Straight	10
LC02FBR-PVC	PVC	PVC	4/0.34	Elbow	2
LC05FBR-PVC	PVC	PVC	4/0.34	Elbow	5
LC10FBR-PVC	PVC	PVC	4/0.34	Elbow	10
LC02FBR-PUR	PUR	PVC	4/0.34	Elbow	2
LC05FBR-PUR	PUR	PVC	4/0.34	Elbow	5
LC10FBR-PUR	PUR	PVC	4/0.34	Elbow	10

Custom versions can be made for particular applications. Please contact Cynergy3 with your requirements.

Mechanical Dimensions



Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969

Email:sales@cynergy3.com

ISO9001 CERTIFIED

www.cynergy3.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sensata:

[LC02FBR-PUR](#) [LC02FBR-PVC](#) [LC02FBS-PUR](#) [LC02FBS-PVC](#) [LC05FBR-PUR](#) [LC05FBR-PVC](#) [LC05FBS-PUR](#)
[LC05FBS-PVC](#) [LC10FBR-PUR](#) [LC10FBR-PVC](#) [LC10FBS-PUR](#) [LC10FBS-PVC](#)