


Technical Data Sheet

Rosenberger

RPC-N
50 Ω

Termination
Plug

05S150-010S3



All dimensions are in mm; tolerances according to ISO 2768 m-H

Interface

According to IEC 61169-16

Documents

N/A

Material and plating

Connector parts

Center conductor
Outer conductor
Coupling nut
Dielectric
Substrate

Material

CuBe
Stainless steel
Stainless steel
PPE
 Al_2O_3

Plating

Gold, min. 1.27 μm , over nickel
Passivated
Passivated

Dieses Dokument ist urheberrechtlich geschützt • This document is protected by copyright • Rosenberger Hochfrequenztechnik GmbH & Co. KG
RF_35/05.10/6.0

Technical Data Sheet				Rosenberger			
RPC-N 50 Ω		Termination Plug		05S150-010S3			
Electrical data Frequency rangeDC to 18 GHz Return loss≥ 28 dB, DC to 18 GHz DC Resistance50 Ω ± 0.25 Ω Power handling≤ 1 W Mechanical data Mating cycles≥ 500 Maximum torque1.70 Nm Recommended torque1.10 Nm Gauge5.28 mm to 5.36 mm Environmental data Operating temperature range-40 °C to +85 °C Storage temperature range-40 °C to +85 °C RoHScompliant Packing Standard1 pce in box Weight54.1 g/pce							
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	02/08/04	Lars Ramtke	19/03/15	e00	15-0329	Marion Striegler	19/03/15
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de				Tel. : +49 8684 18-0 Email : info@rosenberger.de			Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[05S150-010S3](#)