




All dimensions are in mm; tolerances according to ISO 2768 m-H

Documents

Application note

AN001 "Calibration Services"

Material and plating

Connector parts

Center and outer contact
Gauge block coupling nut
Gauge block body

Material

Stainless steel
Stainless steel
Stainless steel

Plating

N/A
Passivated
N/A

Mechanical data

Gauge block nominal gauge	5.28 mm
Gauge range	5.28 mm $\pm$ 0.5 mm
Scale gradation	1 μ m
Limit of measurement error ^{1, 2}	$\leq$ 10 μ m
Typical measurement error ^{1, 2}	$\leq$ 6 μ m
Measuring force	1.5 N

¹ When zeroed with gauge block

² 5.24 mm to 5.40 mm

Technical Data Sheet				Rosenberger			
RPC-TNC		Gauge Plug		06W00S-000			
Declaration of calibration options Factory Calibration Standard delivery for this gauge includes a Factory Calibration. The Calibration Certificate issued reports individual mechanical calibration results, traceable to national / international standards. Accredited Calibration Not available. For further, more detailed information see application note AN001 on the Rosenberger homepage.							
Calibration interval Recommendation				12 months			
Packing Standard Weight				1 pce in box 206.8 g/pce			
While the information has been carefully compiled to the best of our knowledge, nothing is intended as representation or warranty on our part and no statement herein shall be construed as recommendation to infringe existing patents. In the effort to improve our products, we reserve the right to make changes judged to be necessary.							
Draft	Date	Approved	Date	Rev.	Engineering change number	Name	Date
Herbert Babinger	02.03.05	Martin Moder	08.03.19	h00	19-0388	S. Schmid	06.03.19
Rosenberger Hochfrequenztechnik GmbH & Co. KG P.O.Box 1260 D-84526 Tittmoning Germany www.rosenberger.de					Tel. : +49 8684 18-0 Email : info@rosenberger.de		Page 2 / 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Rosenberger:](#)

[06W00S-000](#)