

SC-ISOSLICE-7

ISOLATED BUS I/O MODULE



- 2 off Frequency Inputs or 1 off Pulse Counting Input
- Communicates to Ethernet / RS232 or RS485 network via an SC-E-100 unit
- Input/Output/Power Supply Isolation
- Automatic Bus & Power Connection Via DIN Rail Bus Connector
- Multiple inputs in one module
- Very High Accuracy, Low Cost

Input Types for SC-ISOSLICE-7

Frequency Inputs x 2 or
Pulse Counting Input x 1

Outputs

For Output Modules see SC-ISOSLICE-6 or
SC-ISOSLICE-8

The type of digital input can be selected using internal DIP switches.

Typical inputs are volt free contacts or 0-24 Volt

The standard maximum frequency is 10kHz per channel but higher frequencies may be available, please enquire.

The SC-ISOSLICE-7 isolated Bus I/O module combines full three-port isolation with access to an industrial bus. This bus connects to the SC-E-100 modules which are then used to transmit the process values via either an Ethernet or a RS232/485 wired communications network.

Full 3-port isolation is standard but for channel to channel isolation please see the SC-ISOSLICE-1.

The frequency or pulse counting input type can be switched using internal DIP switches for either volt-free contact inputs or voltage level inputs. The two frequency input values or one pulse counting total can be read from internal modbus registers.

The units have a wide ranging 12 to 36 Vdc. This supply can either be wired to the appropriate terminals or picked up automatically from the Bus connector.

Technical Specifications

Parameter	Min	Typ	Max	Comments
Supply Voltage	12V	24V	36Vdc	
Supply Current (mA)		45	90	For 24Vdc supply (260mA for 50ms on start-up)
Bus Connection				16-bit bus connection
Temp Coefficient			±50ppm/°C	
Time Constant (10-90%)		60mS (normal)		200mS for reading update
Operating Ambient	0°C		55°C	
Relative Humidity	0%		90%	
Isolation Voltage ^{see note}	1kV			
Surge Voltage	2.5kV for 50µS		Transient of 10kV/µS	

Notes


Absolute maximum ratings indicate sustained limits beyond which damage to the device may occur.
Device is protected against reverse polarity connection.
Accuracy figures based on 24Vdc supply, 4-20mA output with 250Ω load and an ambient 20°C.

Installation Data

Mounting	DIN Rail TS35
Orientation	Any
Connections	Screw Clamp with pressure plate
Conductor Size	0.5-4.0mm
Insulation Stripping	12mm
Weight	Approx 95g

Ordering Information

Part No.: SC-ISOSLICE-7



Part Number	Universal Inputs	mA or V Inputs	RTD Inputs	T/C Inputs	Analogue Outputs	Digital Inputs	Digital Outputs
SC-ISOSLICE-1	2						
SC-ISOSLICE-2		8					
SC-ISOSLICE-3			4				
SC-ISOSLICE-4				4			
SC-ISOSLICE-5						8	
SC-ISOSLICE-6							4
SC-ISOSLICE-7						2 x freq in	
SC-ISOSLICE-8					4		
SC-ISOSLICE-9	4 x AC I/V						

Cynergy3 Components Ltd.
7 Cobham Road
Ferndown Industrial Estate
Wimborne, Dorset BH21 7PE
Telephone +44 (0) 1202 897969
Email:sales@cynergy3.com

ISO9001 CERTIFIED

SC-ISOSLICE-7 2017



www.cynergy3.com

© 2017 Cynergy3 Components, All Rights Reserved. Specifications are subject to change without prior notice. Cynergy3 Components and the Cynergy3 Components logo are trademarks of Cynergy3 Components Limited.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sensata:

[SC-ISOSLICE-7](#)